



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## PLVWHT34 Rhino 3/4" White Vinyl

*Newell (Dymo)*

|                  |   |
|------------------|---|
| Catalog Number   | PLVWHT34  |
| Manufacturer     | Newell (Dymo)   |
| Description      | Component Label, Permanent Acrylic Adhesive Type; Vinyl Material; 18 Foot; 3/4 Inch; Indoor/Outdoor Application; 178 Micrometer Thickness; White Background Color; Thermal Transfer Printer Type; Black Graphic Color; Rohs Compliant |
| Weight per unit  | N/A   |
| Product Category | Markers & Marking Tapes   |

### Features

|               |                  |
|---------------|------------------|
| Graphic Color | BLACK            |
| Material      | Vinyl            |
| Printer Type  | THERMAL TRANSFER |

### Material, Color, and Finish

|                  |       |
|------------------|-------|
| Background Color | White |
|------------------|-------|

### Dimensions and Weight

|           |                |
|-----------|----------------|
| Length    | 18 Foot        |
| Thickness | 178 Micrometer |
| Width     | 3/4 INCH       |

### Descriptions

|                        |   |
|------------------------|---|
| Additional Information | RoHS Compliant; Used On Rhino 6000 Dynamometer; Applicable Standard UL 969, ANSI, OSHA, ISO   |
| Commodity Description  | Markers & Marking Tapes   |
| Description            | RHINO 3/4" WHITE VINYL  |
| extra long description | PERMANENT ACRYLIC ADHESIVE TYPE; VINYL MATERIAL; 18 FOOT; 3/4 INCH; INDOOR, OUTDOOR, ASSETS AND BARCODING, WIRE AND CABLE, NETWORK COMPONENT APPLICATION; 178 MICROMETER THICKNESS; WHITE BACKGROUND COLOR; THERMAL TRANSFER PRINTER TYPE; BLACK GRAPHIC COLOR; ROHS COMPLIANT; CONSTRUCTIONAL FEATURE MOISTURE, CHEMICAL AND UV RESISTANT; USED ON RHINO 6000 DYNAMOMETER; APPLICABLE STANDARD UL 969, ANSI, ISO, OSHA |
| Long Description       | COMPONENT LABEL, PERMANENT ACRYLIC ADHESIVE TYPE; VINYL MATERIAL; 18 FOOT; 3/4 INCH; INDOOR/OUTDOOR APPLICATION; 178 MICROMETER THICKNESS; WHITE BACKGROUND COLOR; THERMAL TRANSFER PRINTER TYPE; BLACK GRAPHIC COLOR; ROHS COMPLIANT   |
| Product Type           | Component Label   |



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

|                           |                |
|---------------------------|----------------|
| Brand                     | DYMO           |
| GTIN                      | 00071701184450 |
| Manufacturers Part Number | 18445          |
| UPC                       | 071701184450   |

## Taxonomies, Classifications, and Categories

|                      |                            |
|----------------------|----------------------------|
| Category Description | TAPE                       |
| Type                 | Permanent Acrylic Adhesive |

## Packaging

|                 |   |
|-----------------|---|
| Carton          | 1 |
| Weight Per each | 0 |

## Uses, Certifications, and Standards

|             |                |
|-------------|----------------|
| Application | Indoor/Outdoor |
|-------------|----------------|