



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PN108FL #10 Nyl FK Term *Panduit Corporation*

| | |
|------------------|---|
| Catalog Number | PN108FL |
| Manufacturer | Panduit Corporation |
| Description | The PN10-8F-L Pan-Term® Terminal Is A Nylon Insulated, Fork Terminal. The Metal Insulation Grip Sleeve Crimps to Wire Insulation, Providing Protection and Strain Relief to The Crimp Joint For High Vibration Applications. Barrel Serrations Assure Good Wire Contact and Maximum Tensile Strength. |
| Weight per unit | 0.0006 (lbs/each) |
| Product Category | Small Terminals & Connectors |

Features

| | |
|----------------|----------|
| connection | Standard |
| insulation | Nylon |
| Material | Copper |
| media | Yes |
| Voltage Rating | 600 |
| Wire Size | 10 |

Material, Color, and Finish

| | |
|--------|--------|
| Color | Yellow |
| Finish | Tinned |

Dimensions and Weight

| | |
|------|----|
| Size | #8 |
|------|----|

Descriptions

| | |
|------------------------|---|
| Description | #10 NYL FK TERM |
| extra long description | PAN PN10-8F-L Pan-Term® PN10-8F-L F |
| Long Description | The PN10-8F-L Pan-Term® Terminal is a nylon insulated, fork terminal. The metal insulation grip sleeve crimps to wire insulation, providing protection and strain relief to the crimp joint for high vibration applications. Barrel serrations assure good wire contact and maximum tensile strength. |
| Product Type | Pan-Term® PN10-8F-L Fork Terminal, Yellow, Nylon, 10-12 Awg, |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | PANDUIT |
| GTIN | 00074983803187 |
| Manufacturers Part Number | PN108FL |
| UPC | 074983803187 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description TERMINALS

Type Fork Terminal

Packaging

Carton 50

Package 250

Weight Per each 0.0006

Uses, Certifications, and Standards

Enclosure Fork shape

Mounting 9/32

standard CSA Certified LR31212;UL Listed 587H E52164

Temperature Rating 221 Degrees Fahrenheit (105 Degrees Celsius)