



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PS20AC1RPL 20A 120VAC B+S Wire SP Pilot Red

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | PS20AC1RPL |
| Manufacturer | Pass & Seymour/Legrand |
| Description | 1-Pole Pilot Lighted Switch, Back and Side-Wire, 20A 277V |
| Weight per unit | 0.2142 (lbs/each) |
| Product Category | Gen Purpose Switches |

Features

| | |
|-----------------|---------------|
| action | Single pole |
| amperage rating | 20 |
| Contact Rating | 20Amp, 120Vac |
| insulation | False |
| Poles | Single Pole |
| Switch Type | Toggle |
| Voltage | 120.0 V |
| Voltage Rating | 120 |

Dimensions and Weight

| | |
|------|--------|
| Size | 3.3 in |
|------|--------|

Descriptions

| | |
|------------------------|---|
| Description | 20A 120VAC B+S WIRE SP PILOT RED |
| extra long description | P&S PS20AC1RPL 20A 120VAC B+S WIRE |
| Long Description | 1-Pole Pilot Lighted Switch, Back and Side-Wire, 20A 277V |
| Product Type | 20A 120VAC B+S Wire SP Pilot Red |
| Special Features | Lighted when off, back & side wire, locking support heavy duty toggle |

Manufacturer Information

| | |
|---------------------------|------------------|
| Brand | Pass and Seymour |
| GTIN | 00785007195842 |
| Manufacturers Part Number | PS20AC1RPL |
| UPC | 785007195842 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|---------------------|
| Category Description | Commercial switches |
| Type | Pilot Toggle Switch |

Trade Size

| | |
|----------|------|
| Amperage | 20.0 |
|----------|------|

Packaging

| | |
|-----------------|--------|
| Carton | 10 |
| Package | 50 |
| Weight Per each | 0.2142 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------|---------------------------|
| Application | Industrial Spec Grade |
| Enclosure | Nylon |
| Mounting | WALL |
| standard | CULUS, FEDSPEC, UL 498/20 |