



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PS20AC4BK 20A 120/277VAC B+S Wire 4W SW BK

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | PS20AC4BK |
| Manufacturer | Pass & Seymour/Legrand |
| Description | 4-Way Toggle Switch, Back and Side-Wire, 20A 120/277V |
| Weight per unit | 0.2260 (lbs/each) |
| Product Category | Gen Purpose Switches |

Features

| | |
|-----------------|-------------------|
| amperage rating | 20 |
| Contact Rating | 20Amp, 120/277Vac |
| insulation | False |
| Poles | 4-Way |
| Voltage | 120.0 V |
| Voltage Rating | 120/277 |
| Wattage | 4 |
| Wire Size | #14 - #10 Awg |

Material, Color, and Finish

| | |
|--------|-------|
| Finish | Matte |
|--------|-------|

Dimensions and Weight

| | |
|------|------|
| Size | 3.3" |
|------|------|

Descriptions

| | |
|------------------------|--|
| Description | 20A 120/277VAC B+S WIRE 4W SW BK |
| extra long description | P&S PS20AC4BK 20A 120/277VAC B+S WI |
| Long Description | 4-Way Toggle Switch, Back and Side-Wire, 20A 120/277V |
| Product Type | 20A 120/277VAC B+S Wire 4W SW BK |
| Special Features | High strength toggle, heavy duty toggle bumpers, locking support |

Manufacturer Information

| | |
|---------------------------|------------------------|
| Brand | LEGRAND-PASS & SEYMOUR |
| GTIN | 00785007195460 |
| Manufacturers Part Number | PS20AC4-BK |
| UPC | 785007195460 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------|
| Category Description | Residential plates |
| Type | SWITCH |

Trade Size

| | |
|----------|------|
| Amperage | 20.0 |
|----------|------|



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Package | 50 |
| Weight Per each | 0.226 |

Uses, Certifications, and Standards

| | |
|----------------------|---|
| Application | Industrial |
| Mounting standard | WALL CSA, FEDSPEC, CULUS, UL, UL 20, FEDSPEC |