



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PS20AC4L 20A 120/277VAC B+S Wire 4W Lock SW Gy

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | PS20AC4L |
| Manufacturer | Pass & Seymour/Legrand |
| Description | 4-Way Lock Switch, Back and Side-Wire, 20A 120/277V |
| Weight per unit | 0.2260 (lbs/each) |
| Product Category | Gen Purpose Switches |

Features

| | |
|-----------------|-----------------|
| action | 4P |
| amperage rating | 20 |
| Contact Rating | 120/277V, 20Amp |
| insulation | False |
| Poles | 4-Way |
| Switch Type | Toggle |
| Voltage | 120.0 V |
| Voltage Rating | 120/277 |

Dimensions and Weight

| | |
|------|------|
| Size | 3.3" |
|------|------|

Descriptions

| | |
|------------------------|---|
| Description | 20A 120/277VAC B+S WIRE 4W LOCK SW GY |
| extra long description | P&S PS20AC4L 20A 120/277VAC B+S WIR |
| Long Description | 4-Way Lock Switch, Back and Side-Wire, 20A 120/277V |
| Product Type | 20A 120/277VAC B+S Wire 4W Lock SW Gry |
| Special Features | Heavy duty switch, back & side wire, with lock |

Manufacturer Information

| | |
|---------------------------|------------------------|
| Brand | LEGRAND-PASS & SEYMOUR |
| GTIN | 00785007195644 |
| Manufacturers Part Number | PS20AC4-L |
| UPC | 785007195644 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|-----------------------------------|
| Category Description | Miscellaneous residential devices |
| Type | SWITCH |

Trade Size

| | |
|----------|------|
| Amperage | 20.0 |
|----------|------|

Packaging

| | |
|-----------------|-------|
| Carton | 1 |
| Package | 50 |
| Weight Per each | 0.226 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------------|-------------------------------------|
| Application | Commercial/Residential |
| Mounting | WALL |
| standard | FEDSPEC, CULUS, CSA, UL, UL20 |