
20A, 125V EXTRA-HARD USE HOSPITAL- GRADE CONNECTOR, BLACK & CLEAR

PS5369XHG | [Pass & Seymour](#)



FEATURES & BENEFITS

Straight Blade Connector 2pole 3wire 20amp 125volt Hospital Grade



- Unit arrives completely ready-to-wire, cuts installation time significantly.
- Nylon housing provides impact and chemical resistance.
- Rugged two-piece cord grip provides more uniform cord retention.
- Internal dust shield keeps terminals free of contaminants.
- Tri-drive assembly screws are standard on Hospital Grade plugs and connectors (angle plugs not included).
- All 3-wire terminals located on the same plane, allows for quick wire termination from any angle.
- Heavy-duty brass alloy blades and contacts, resist heat rise, provide excellent conductivity.
- Cord-grip screws recessed to protect installer against screwdriver head slippage.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Black

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: No
CUL Listing No: No
cULus: Yes
cURus: No
Federal Spec: Yes
UL Listing No: No
UN SPSC: 39121402
UR: No

DIMENSIONS

Depth (US): 2.638"

Height (US): 1.516"

Width (US): 1.516"

TECHNICAL INFORMATION

Volts (AC): 125

Grade Type: Hospital

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant



20A, 125V EXTRA-HARD USE HOSPITAL- GRADE CONNECTOR, BLACK & CLEAR

PS5369XHG | [Pass & Seymour](#)



FEATURES & BENEFITS

Straight Blade Connector 2pole 3wire 20amp 125volt Hospital Grade



- Unit arrives completely ready-to-wire, cuts installation time significantly.
- Nylon housing provides impact and chemical resistance.
- Rugged two-piece cord grip provides more uniform cord retention.
- Internal dust shield keeps terminals free of contaminants.
- Tri-drive assembly screws are standard on Hospital Grade plugs and connectors (angle plugs not included).
- All 3-wire terminals located on the same plane, allows for quick wire termination from any angle.
- Heavy-duty brass alloy blades and contacts, resist heat rise, provide excellent conductivity.
- Cord-grip screws recessed to protect installer against screwdriver head slippage.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Color: Black

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

CSA Listing Info: No
CUL Listing No: No
cULus: Yes
cURus: No
Federal Spec: Yes
UL Listing No: No
UN SPSC: 39121402
UR: No

DIMENSIONS

Depth (US): 2.638"

Height (US): 1.516"

Width (US): 1.516"

TECHNICAL INFORMATION

Volts (AC): 125

Grade Type: Hospital

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO

Buy American Act Status: Trade Agreement Act Compliant

