

Eaton PSG240F24RM

Catalog Number: PSG240F24RM

Eaton Power Supply, Three-phase, 24 Vdc, 240W, IP20, Term metal

General specifications



Photo is representative

Product Name	Catalog Number
Eaton PSG general purpose power supply	PSG240F24RM
	UPC
	786685683591
Product Length/Depth	Product Height
4.6 in	2.76 in
Product Width	Product Weight
4.76 in	1.2 lb
Certifications	
UL/CUL listed	

defaultTaxonomyAttributeLabel

Power consumption

240 W

Phase

Three-phase

Output voltage

24 V

Degree of Protection

IP20

Resources

Brochures

[Eaton's PSG Series Power Supplies](#)

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Drawings

[PSG240F24RM AutoCAD 2D Footprint](#)

[PSG240F24RM 3D Inventor](#)

[PSG240F24RM AutoCAD 2D Footprint \(mm\)](#)

[PSG240F24RM 2D Drawing Xchange](#)

[PSG240F24RM 2D PDF](#)

[PSG240F24RM 3D Model Xchange](#)

Installation instructions

[Installation Instructions for PSG240F Power Supply](#)

Multimedia

[How to size and select a Power Supply](#)

Specifications and datasheets

[Eaton Specification Sheet - PSG240F24RM](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton PSG240F24RM

Catalog Number: PSG240F24RM

Eaton Power Supply, Three-phase, 24 Vdc, 240W, IP20, Term metal

General specifications



Photo is representative

Product Name	Catalog Number
Eaton PSG general purpose power supply	PSG240F24RM
	UPC
	786685683591
Product Length/Depth	Product Height
4.6 in	2.76 in
Product Width	Product Weight
4.76 in	1.2 lb
Certifications	
UL/CUL listed	

defaultTaxonomyAttributeLabel

Power consumption

240 W

Phase

Three-phase

Output voltage

24 V

Degree of Protection

IP20

Resources

Brochures

[Eaton's PSG Series Power Supplies](#)

Catalogs

[Eaton's Volume 7—Logic Control, Operator Interface and Connectivity Solutions](#)

Drawings

[PSG240F24RM AutoCAD 2D Footprint](#)

[PSG240F24RM 3D Inventor](#)

[PSG240F24RM AutoCAD 2D Footprint \(mm\)](#)

[PSG240F24RM 2D Drawing Xchange](#)

[PSG240F24RM 2D PDF](#)

[PSG240F24RM 3D Model Xchange](#)

Installation instructions

[Installation Instructions for PSG240F Power Supply](#)

Multimedia

[How to size and select a Power Supply](#)

Specifications and datasheets

[Eaton Specification Sheet - PSG240F24RM](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



Eaton.com/socialmedia