



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PT40 4/0 to 1/0 Reducer *Nsi Industries*

Catalog Number	PT40
Manufacturer	Nsi Industries
Description	Stranded Bi-Metallic Pin Terminal 4/0 Awg Stranded Bi-Metallic Pin Terminals Is Designed to Facilitate Termination Of Aluminum Conductors. Tin-Plated Stranded Copper Pin. Connector Bores Are Coated With Oxide Inhibitor. Supplied With Epdm Insulating Cover. Ul 486B Listed. Rated 600 Volts.
Weight per unit	0.2400 (lbs/each)
Product Category	Large Terminals & Connectors

Features

connection	2/0 Pin
insulation	Plastisol Cover
Material	Aluminum - Tin Plated Copper Pin
Number of Conductors	1
Poles	1
Voltage Rating	600 V
Warranty	1 YEAR

Material, Color, and Finish

Color	White
Finish	Tin Plated

Dimensions and Weight

Size	L=3.52 - OD=.900 - ID=.547 - Pin Dia=.405
------	---

Descriptions

Description	4/0 TO 1/0 REDUCER
extra long description	NSI PT4/0 Aluminum Pin Terminal Cu
Features	Stranded Bi-Metallic Pin Terminal 4/0 AWG Stranded Bi-Metallic Pin Terminals is designed to facilitate termination of aluminum conductors. Tin-plated stranded copper pin. Connector bores are coated with oxide inhibitor. Supplied with EPDM insulating cover. UL 486B listed. Rated 600 volts.
Long Description	Stranded Bi-Metallic Pin Terminal 4/0 AWG Stranded Bi-Metallic Pin Terminals is designed to facilitate termination of aluminum conductors. Tin-plated stranded copper pin. Connector bores are coated with oxide inhibitor. Supplied with EPDM insulating cover. UL 486B listed. Rated 600 volts.
Product Type	Aluminum Pin Terminal Cu Pin 4/0 Awg
Special Features	4/0 AWG (STR) - 2/0 CU Pin Size



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	NSi
GTIN	00662381033079
Manufacturers Part Number	PT4/0
UPC	662381033079

Taxonomies, Classifications, and Categories

Category Description	Comp & Mech Lugs and Butt Splices
Type	Bi-Metallic Pin

Packaging

Carton	1
Weight Per each	0.24

Uses, Certifications, and Standards

Application	Terminate, Splice, Tap Power Connectors
environmental conditions	90 C
standard	UL486A/B
Temperature Rating	90 C