



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PT5362W Duplex Recp Spec GRD 20A/125V WH

Pass & Seymour/Legrand

Catalog Number	PT5362W
Manufacturer	Pass & Seymour/Legrand
Description	Plugtail Registered Spec Grade Receptacles, 20A, 125V Plugtail Registered Devices and Connectors Mean That Device Installation Is The Same Regardless Of Skill Level Of The Installer. The UI-Listed Connectors Are Keyed to Ensure Proper Wiring Installation Into Each Receptacle.
Weight per unit	0.2300 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20
connection	Wire Ground
indoor/outdoor	Indoor
media	Yes
Number of Wires	3
Outlet Type	Commercial, Indoor
Poles	2
Voltage	125.0 V
Voltage Rating	125
Wire Size	4

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Size	3.3 in
------	--------

Descriptions

Description	DUPLEX RECP SPEC GRD 20A/125V WH
extra long description	P&S PT5362W DUP RECEPT SPEC GRADE 2
Long Description	PlugTail Registered Spec Grade Receptacles, 20A, 125V PlugTail Registered devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each receptacle.
Product Type	Dup Recept Spec Grade 20A/125V W
Special Features	Crimped & welded contacts, no exposed terminals, finger safe application



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Pass and Seymour
GTIN	00785007091724
Manufacturers Part Number	PT5362-W
UPC	785007091724

Taxonomies, Classifications, and Categories

Category Description	Commercial receptacles
Type	Outlet

Trade Size

Amperage	20.0
----------	------

Packaging

Carton	1
Package	100
Weight Per each	0.23

Uses, Certifications, and Standards

Application	Commercial
Mounting	WALL
nema rating	5-15R
standard	CULUS, UL 498, FEDSPEC