



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PT8300HW PT Hosp GRD Compact Design Recp 20A/125V WH

Pass & Seymour/Legrand

Catalog Number	PT8300HW
Manufacturer	Pass & Seymour/Legrand
Description	20A 125V Plugtail Hospital Grade Duplex Receptacle White
Weight per unit	0.1960 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20
connection	PlugTail
Dielectric Strength	Withstands 2000V minimum
indoor/outdoor	Indoor
media	Yes
Number of Wires	3
Outlet Type	Commercial, Indoor
Phase	1
Poles	Double Pole
Voltage	125.0 V
Voltage Rating	125
Wire Size	12

Material, Color, and Finish

Finish	Matte
--------	-------

Dimensions and Weight

Depth	1.225
Height	3.82
Width	1.750

Descriptions

Description	PT HOSP GRD COMPACT DESIGN RECP 20A/125V WH
extra long description	P&S PT8300HW PT HG COMPACT DESIGN R
Long Description	20A 125V Plugtail Hospital Grade Duplex Receptacle White
Product Type	PT HG Compact Design Recept 20A/125V W
Special Features	Factory-terminated devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each hospital-grade receptacle. The connector simply snaps into the back of the device—information, visit our PlugTail Headquarters.;no fussing with wires, stripping or tightening screws. PlugTail devices are finger safe with no exposed terminals, so taping is not required. Now installation is a sna



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007091434
Manufacturers Part Number	PT-8300HW
UPC	785007091434

Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Outlet

Trade Size

Amperage	15.0
----------	------

Packaging

Carton	1
Package	100
Weight Per each	0.196

Uses, Certifications, and Standards

Application	Commercial
environmental conditions	UL94 V2
Mounting	BOX
nema rating	5-20R
standard	CULUS, FEDSPEC, CSA Lsied, CUL, FSUL, UL Listed