



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PT20AC1RED PT 20A 120/277V SP SW RD

Pass & Seymour/Legrand

| | |
|------------------|---|
| Catalog Number | PT20AC1RED |
| Manufacturer | Pass & Seymour/Legrand |
| Description | Plugtail® Single-Pole 20A Toggle Switch |
| Weight per unit | 0.1868 (lbs/each) |
| Product Category | Gen Purpose Switches |

Features

| | |
|-----------------|-------------------|
| amperage rating | 20 |
| Contact Rating | 20Amp, 120/277Vac |
| insulation | False |
| media | Yes |
| Poles | Single Pole |
| Voltage | 120.0 V |
| Voltage Rating | 120/277 |
| Wattage | 1 |

Dimensions and Weight

| | |
|------|------|
| Size | 3.3" |
|------|------|

Descriptions

| | |
|------------------------|--|
| Description | PT 20A 120/277V SP SW RD |
| extra long description | P&S PT20AC1RED PT 20A 120/277V SP S |
| Long Description | PlugTail® Single-Pole 20A Toggle Switch |
| Product Type | PT 20A 120/277V SP SW Red |
| Special Features | Built in connector, glass reinforced nylon back body, shallow design |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Pass & Seymour |
| GTIN | 00785007108620 |
| Manufacturers Part Number | PT20AC1-RED |
| UPC | 785007108620 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--------------------|
| Category Description | Residential plates |
| Type | PLUG TAIL SWITCH |

Trade Size

| | |
|----------|------|
| Amperage | 20.0 |
|----------|------|

Packaging

| | |
|-----------------|--------|
| Carton | 1 |
| Package | 50 |
| Weight Per each | 0.1868 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------|-------------------------------|
| Application | Commercial |
| Mounting | WALL |
| standard | CULUS, FEDSPEC, cULus, WS8996 |