



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PT8300HLA PT Hosp GRD Compact Design Recept 20A/125V La

Pass & Seymour/Legrand

Catalog Number	PT8300HLA
Manufacturer	Pass & Seymour/Legrand
Description	20A 125V Plugtail Hospital Grade Duplex Receptacle Light Almond
Weight per unit	0.1850 (lbs/each)
Product Category	Gen Purpose Recept & Surge Pro

Features

amperage rating	20
connection	PlugTail
Dielectric Strength	Withstands 2000V minimum
indoor/outdoor	Indoor
media	Yes
Number of Wires	3
Outlet Type	Indoor, Commercial
Phase	1
Poles	Double Pole
Voltage	125.0 V
Voltage Rating	125
Wire Size	12

Dimensions and Weight

Depth	1.225
Height	3.82
Width	1.750

Descriptions

Description	PT HOSP GRD COMPACT DESIGN RECP 20A/125V LA
extra long description	P&S PT8300HLA PT HG COMPACT DESIGN
Long Description	20A 125V Plugtail Hospital Grade Duplex Receptacle Light Almond
Product Type	PT HG Compact Design Recept 20A/125V La
Special Features	Factory-terminated devices and connectors mean that device installation is the same regardless of skill level of the installer. The UL-Listed connectors are keyed to ensure proper wiring installation into each hospital-grade receptacle. The connector simply snaps into the back of the device—no fussing with wires, stripping or tightening screws. PlugTail devices are finger safe with no exposed terminals, so taping is not required. Now installation is a snap! PlugTail...The toughest and safest hospital...



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Pass & Seymour
GTIN	00785007091410
Manufacturers Part Number	PT8300HLA
UPC	785007091410

Taxonomies, Classifications, and Categories

Category Description	Residential Switches
Type	Outlet

Trade Size

Amperage	15.0
----------	------

Packaging

Carton	1
Package	100
Weight Per each	0.185

Uses, Certifications, and Standards

Application	Commercial
environmental conditions	UL94 V2
Mounting	BOX
nema rating	5-20R
standard	CULUS, FEDSPEC, CSA Lsied, CUL, FSUL, UL Listed