



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PV1500LB58 1-1/2 PVC Coated Form 8

Calpipe Industries, Inc

| | |
|------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Catalog Number | PV1500LB58 |
| Manufacturer | Calpipe Industries, Inc |
| Description | Conduit Body, 0.002 Inch Urethane Coated Interior/0.04 Inch PVC Coated Exterior Steel Material; 10.67 Inch Length X 2.79 Inch Width X 4.07 Inch Height Size; Rigid Conduit Used On; 1-1/2 Inch Hub Size; LB Configuration; 2 Hub(S) |
| Weight per unit | N/A |
| Product Category | PVC Bodies & Boxes |

Features

| | |
|----------------|-------------------------------------------------------------------------|
| Access Opening | BACK |
| Cover Type | PVC Coated Cast Iron, Screw-On |
| Form Type | FORM 8 |
| Hub Location | 90 Degree |
| Material | 0.002 Inch Urethane Coated Interior/0.04 Inch PVC Coated Exterior Steel |
| Number of Hubs | 2 |

Dimensions and Weight

| | |
|----------|--------------------------------------------------------|
| Hub Size | 1-1/2 INCH |
| Size | 10.67 Inch Length x 2.79 Inch Width x 4.07 Inch Height |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

| | |
|------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Additional Information | Enclosure Type NEMA 4X; Constructional Feature Corrosion Resistant; Includes Cover, Plastic Encapsulated Stainless Steel Screw; Application Chemical and Petrochemical Plant, Water and Wastewater Treatment Facility, Pulp and Paper Mill, Cooling Tower, Mini |
| Commodity Description | PVC CONDUIT BODIES,FS BX,JUNCT. BX |
| Description | 1-1/2 PVC COATED FORM 8 |
| extra long description | 0.002 INCH URETHANE COATED INTERIOR/0.04 INCH PVC COATED EXTERIOR MATERIAL; 2.79 INCH WIDTH X 4.07 INCH HEIGHT SIZE; CONDUIT USED ON; 1-1/2 INCH HUB SIZE; LB CONFIGURATION; 2 HUB(S); UL 514B, CSA C22.2 APPROVAL; PVC COATED CAST IRON COVER TYPE; 90 DEGREE HUB LOCATION; FORM 8 FORM TYPE; BACK ACCESS OPENING; ENCLOSURE RATING NEMA 4X; INCLUDES PVC COATED CAST IRON COVER, PLASTIC ENCAPSULATED STAINLESS STEEL SCREW; PV MODEL |
| Long Description | CONDUIT BODY, 0.002 INCH URETHANE COATED INTERIOR/0.04 INCH PVC COATED EXTERIOR STEEL MATERIAL; 10.67 INCH LENGTH X 2.79 INCH WIDTH X 4.07 INCH HEIGHT SIZE; RIGID CONDUIT USED ON; 1-1/2 INCH HUB SIZE; LB CONFIGURATION; 2 HUB(S) |
| Product Type | Conduit Body |

Manufacturer Information

| | |
|---------------------------|-------------------------|
| Brand | Calpipe Industries, Inc |
| GTIN | 00847656074821 |
| Manufacturers Part Number | PV1500LB58 |
| UPC | 847656074821 |

Packaging

| | |
|-----------------|---|
| Carton | 1 |
| Weight Per each | 0 |

Uses, Certifications, and Standards

| | |
|---------------|----------------------|
| Approval | UL 6/514B, CSA C22.2 |
| Configuration | LB |
| Used On | RIGID CONDUIT |