



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## PV4090EL00 4IN PVC Coated Rigid 90

*Calpipe Industries, Inc*

Catalog Number	PV4090EL00
Manufacturer	Calpipe Industries, Inc
Description	PVC Coated Steel Rigid Conduit Standard Radius Elbow, Standard Radius Type; Steel Material; 0.002 Inch Urethane Coated Interior, 0.04 Inch PVC Coated Exterior Finish; UI 6, Cul Approval; Ansi C80.1, Nema RN-1 Applicable Standard; 1 Standard Package
Weight per unit	36.8 (lbs/each)
Product Category	Steel

### Features

Applicable Standard	ANSI C80.1, NEMA RN-1
Bend Angle	90 Degree
Bend Radius	16 INCH
End Type	THREADED
Material	Steel

### Material, Color, and Finish

Finish	0.002 Inch Urethane Coated Interior, 0.04 Inch PVC Coated Exterior
--------	--



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Additional Information	Length 21 Inch; Constructional Feature Corrosion Resistant; Application Petrochemical, Water and Wastewater Treatment Facility, Transportation and Infrastructure, Food, Dairy and Beverage, Mining, Marine and Coastal Facility, Chemical Plants, Steel Mills,
Commodity Description	ELBOWS-COUPPLINGS-NIPPLES - STEEL
Description	4IN PVC COATED RIGID 90
extra long description	STANDARD RADIUS TYPE; STEEL MATERIAL; 0.002 INCH URETHANE COATED INTERIOR, 0.04 INCH PVC COATED EXTERIOR FINISH; UL 6, CUL APPROVAL; ANSI C80.1, NEMA RN-1 APPLICABLE STANDARD; 1 STANDARD PACKAGE; 4 INCH TRADE SIZE; THREADED END TYPE; 90 DEGREE BEND ANGLE; 16 INCH BEND RADIUS; LENGTH 21 INCH; CONSTRUCTIONAL FEATURE CORROSION RESISTANT; APPLICATION PETROCHEMICAL, WATER AND WASTEWATER TREATMENT FACILITY, TRANSPORTATION AND INFRASTRUCTURE, FOOD, DAIRY AND BEVERAGE, MINING, MARINE AND COASTAL FACILITY, CHEMICAL
Long Description	PVC COATED STEEL RIGID CONDUIT STANDARD RADIUS ELBOW, STANDARD RADIUS TYPE; STEEL MATERIAL; 0.002 INCH URETHANE COATED INTERIOR, 0.04 INCH PVC COATED EXTERIOR FINISH; UL 6, CUL APPROVAL; ANSI C80.1, NEMA RN-1 APPLICABLE STANDARD; 1 STANDARD PACKAGE
Product Type	PVC Coated Steel Rigid Conduit Standard Radius Elbow

## Manufacturer Information

Brand	Calpipe Industries, Inc
GTIN	00847656053963
Manufacturers Part Number	PV4090EL00
Model	PV
UPC	847656053963

## Taxonomies, Classifications, and Categories

Category Description	DIECAST EMT FITTINGS
Type	STANDARD RADIUS

## Trade Size

Trade Size	4 INCH
------------	--------

## Packaging

Carton	1
Standard Package	1
Weight Per each	36.75

## Uses, Certifications, and Standards

Approval	UL 6, CUL
----------	-----------