



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## PW301W Pir Wall SWITCH Occ SNSR 120/277V W

*Pass & Seymour/Legrand*

|                  |  |
|------------------|--|
| Catalog Number   | PW301W   |
| Manufacturer     | Pass & Seymour/Legrand   |
| Description      | Wall Switch Occupancy Sensor, Sensor With Relay Type; 1.58 Inch W X 1.39 Inch D X 4.1 Inch H Size; White Finish; UL, Cul Approval; Small Office, Small Conference Room and Lunch/Break Room Application; 120/277 Vac At 50/60 HZ Voltage Rating; Wall Mounting |
| Weight per unit  | 0.4700 (lbs/each)  |
| Product Category | Lighting Occupancy Sensors   |

### Features

|                 |  |
|-----------------|--|
| Area Coverage   | 35 FT X 30 FT (MAJOR MOTION), 20 FT X 15 FT (MINOR MOTION)   |
| Load Rating     | 0 to 1000 W at 120 VAC (Ballast/LED/Tungsten), 0 to 1200 W at 277 VAC (Ballast/LED), 1/6 HP at 120/277 VAC |
| Load Type       | Ballast/Tungsten/LED   |
| Sensor Type     | PASSIVE INFRARED   |
| Terminal Type   | Screw  |
| Time Delay      | 5/10/15/20/25/30 Min   |
| Voltage Rating  | 120/277 VAC AT 50/60 HZ  |
| Wall Plate Type | DECORATOR  |

### Material, Color, and Finish

|        |       |
|--------|-------|
| Finish | white |
|--------|-------|

### Dimensions and Weight

|      |  |
|------|--|
| Size | 1.58 Inch W x 1.39 Inch D x 4.1 Inch H |
|------|--|



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

|                        |   |
|------------------------|---|
| Additional Information | Sensitivity Adjustment PIR (High/Low)   |
| Commodity Description  | LIGHTING OCCUPANCY SENSORS  |
| Description            | PIR WALL SWTCH OCC SNSR 120/277V W  |
| extra long description | SENSOR WITH RELAY TYPE; 1.58 INCH W X 1.39 INCH D X 4.1 INCH H SIZE; WHITE FINISH; UL, CUL APPROVAL; SMALL OFFICE, SMALL CONFERENCE ROOM AND LUNCH/BREAK ROOM APPLICATION; 120/277 VAC AT 50/60 HZ VOLTAGE RATING; WALL MOUNTING; SCREW TERMINAL TYPE; 0 TO 1000 W AT 120 VAC (BALLAST/LED/TUNGSTEN), 0 TO 1200 W AT 277 VAC (BALLAST/LED), 1/6 HP AT 120/277 VAC LOAD RATING; DECORATOR WALL PLATE TYPE; PASSIVE INFRARED SENSOR TYPE; 35 FT X 30 FT (MAJOR MOTION), 20 FT X 15 FT (MINOR MOTION) AREA COVERAGE; BALLAST/TUNGS |
| Long Description       | WALL SWITCH OCCUPANCY SENSOR, SENSOR WITH RELAY TYPE; 1.58 INCH W X 1.39 INCH D X 4.1 INCH H SIZE; WHITE FINISH; UL, CUL APPROVAL; SMALL OFFICE, SMALL CONFERENCE ROOM AND LUNCH/BREAK ROOM APPLICATION; 120/277 VAC AT 50/60 HZ VOLTAGE RATING; WALL MOUNTING  |
| Product Type           | Wall Switch Occupancy Sensor  |

## Manufacturer Information

|                           |                        |
|---------------------------|------------------------|
| Brand                     | Pass & Seymour/Legrand |
| GTIN                      | 00754182935260         |
| Manufacturers Part Number | PW-301-W               |
| UPC                       | 754182935260           |

## Taxonomies, Classifications, and Categories

|                      |                                   |
|----------------------|-----------------------------------|
| Category Description | Miscellaneous residential devices |
| Type                 | SENSOR WITH RELAY                 |

## Packaging

|                 |      |
|-----------------|------|
| Carton          | 1    |
| Package         | 40   |
| Weight Per each | 0.47 |

## Uses, Certifications, and Standards

|             |  |
|-------------|--|
| Application | Small Office, Small Conference Room and Lunch/Break Room |
| Approval    | UL, CUL  |
| Mounting    | WALL   |