



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



PX300S 300 W Pool & Spa Safety Transformer, Stainless Ste

Intermatic Inc.

Catalog Number	PX300S
Manufacturer	Intermatic Inc.
Description	300 W Pool & Spa Safety Transformer, Stainless Steel Enclosure, Input 120V, Output 12, 13, 14 V
Weight per unit	10.5 (lbs/each)
Product Category	Lighting Accessories

Features

Current Rating	3
Input Voltage	120
Output Voltage	12 VAC, 13 VAC, 14 VAC
Wattage	300

Material, Color, and Finish

Color	Silver
-------	--------

Dimensions and Weight

Size	7-1/4 HEIGHT X 5-1/4 WIDTH X 4-1/2 DEPTH IN, 18.4 HEIGHT X 13.3 WIDTH X 11.4 DEPTH CM
------	---

Descriptions

Description	300 W POOL & SPA SAFETY TRANSFORMER, STAINLESS STE
extra long description	INT-MAT PX300S 300 W Pool & Spa Saf
Features	These safety transformers are specifically designed to supply 12-14 VAC and are suitable for direct connection to underwater pool/spa lights. A grounded shield between the primary and secondary winding assures safe operation. Built-in circuit protection will disconnect power to the transformer in case of an overload.
Long Description	300 W Pool & Spa Safety Transformer, Stainless Steel Enclosure, Input 120V, Output 12,13,14 V
Product Type	300 W Pool & Spa Safety Transformer, Stainless Steel Enclosu
Special Features	Features: Built-In Circuit Protection will Disconnect Power to the Transformer in Case of Defect or Overload

Manufacturer Information

Brand	Intermatic Inc.
GTIN	00078275067578
Manufacturers Part Number	PX300S
UPC	078275067578

Taxonomies, Classifications, and Categories

Type	Safety Transformer
------	--------------------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	10.5

Uses, Certifications, and Standards

Application	Pool or Garden Lighting, Spa Lighting, Fountain Lighting
Enclosure	Type 3R Stainless Steel
environmental conditions	OUTDOOR
Frequency Rating	60
Mounting	Bracket Mount
standard	cCSAus Certified