



Preset Dimmers





 Push off/on to selected light level
 Select light level

Switches













General purpose switching of all lighting sources and motor loads
 15A, 120/277V
 Push on/off

Installation Considerations




2.50" Deep Backbox Recommended (minimum)
 Control Depth ≤ 1.44" (37mm)

Description	Maximum Capacity*	Model #	Important Information
<h2>Dimmers</h2>			<p>Ships in 48 hrs.</p> <p>Color Palette Matte Finish Add color suffix to model # Example: Q-600P-WH</p> <p>WH White IV Ivory AL Almond LA Light Almond</p> <p><i>Colors meet NEMA color standards where standards exist</i></p>
 <h3>Incandescent</h3>			
<h4>Preset Dimmers</h4>			
Single Pole	600W	Q-600P- 	
Single Pole	1000W	Q-10P- 	
3-Way	600W	Q-603P- 	
3-Way	1000W	Q-103P- 	
<p><i>Products Above:</i> Use 3-way dimmer with Qoto Q-3PS- or other mechanical switches. Derating required if ganged, pg.95.</p>			
 <h3>Magnetic Low Voltage</h3>			
<h4>Preset Dimmers</h4>			
Single Pole	600VA (450W)	QLV-600P- 	
3-Way	600VA (450W)	QLV-603P- 	
<p><i>Products Above:</i> Wattage indicates maximum lamp load, see Dimming Basics, pg.156. Use 3-way dimmer with Qoto Q-3PS- or other mechanical switches. Derating required if ganged, pg.95.</p>			
<h2>Switches</h2>			
<h3>General Purpose Switching of All Lighting Sources and Motor Loads</h3>			
<h4>Switches</h4>			
Single Pole, 120/277V	15A	Q-1PS- 	
3-Way, 120/277V	15A	Q-3PS- 	
<p><i>Products Above:</i> No derating required if ganged.</p>			



Wallplates
 Wallplates sold separately. Use Fassada™ Fashion Wallplates, pg.92, or standard wallplates.

What's Included

 Control with screw and push-in terminals

***Maximum Capacities**
 For capacities in multigang installations, see ganging and derating information, pg.95.

Controls are 120V 60Hz unless noted.



Global Ordering see pg.185
For More Information:
www.lutron.com/qoto
 Fax-on-Demand 1-800-523-9466



The Dimmer that Replaces Your Toggle Switch with a New Look



Shown actual size: Qoto single-pole dimmer in white (WH). Fassada™ Fashion Wallplate sold separately, pg.92.

Product Family Features

- Elegant oval button and smooth linear-slide dimmer for a traditional wallplate opening
- Includes a general purpose switch for all lighting sources and motor loads
- True 3-way dimming— never lose your ability to dim
- Preset dimmer
- Models feature screw and push-in terminals
- Uses standard single-pole and 3-way wiring for easy installation

Specification Features

(See Performance Specifications, pg. 148)

- Electrostatic discharge protection
- Captive button and slider
- Square law dimming
- Mechanical air-gap switch to disconnect load power
- Includes radio frequency interference suppression circuitry
- Power-failure memory
- Precise color consistency
- UV stable color

Color Palette *(For latest color information, visit www.lutron.com)*

