



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



QBGFT1025 Type QB, 5MA GF Breaker 25A /1 Pole 120/240V, 10K *Eaton Corp*

Catalog Number	QBGFT1025
Manufacturer	Eaton Corp
Description	Eaton QB Gfci Circuit Breaker, Ground Fault Circuit Breaker, 25A, 10 Kaic, Single-Pole, 120/240V, Non-Interchangeable, 5 Ma Trip Sensitivity, QBGF
Weight per unit	0.5000 (lbs/each)
Product Category	On Circuit Breakers

Features

dimensions	1.0000 IN X 1.0000 IN X 1.0000 IN
interrupt rating	10
Poles	1
Voltage Rating	120/240 V

Descriptions

Description	TYPE QB, 5MA GF BREAKER 25A /1 POLE 120/240V, 10K
extra long description	ETN QBGFT1025 QB, 5MA GF 25A /1 POL
Features	Eaton has a wide selection of UL rated miniature circuit breakers for loadcenters, fuseboxes, or similar devices. Each pole provides steel frame calibration and arc chutes with 5 - 100A continuous in one-, two-, and three-pole designs. A full-range of accessories expand customization options, including various mounting and ring tung termination options.
Long Description	Eaton QB GFCI circuit breaker,Ground fault circuit breaker,25A,10 kAIC,Single-pole,120/240V,Non-Interchangeable,5 mA Trip sensitivity,QBGF
Product Type	QB, 5MA GF 25A /1 Pole 120/240V, 10kaic
Special Features	5 mA Trip Sensitivity

Manufacturer Information

Brand	Eaton
GTIN	00786680130977
Manufacturers Part Number	QBGFT1025
UPC	786680130977

Taxonomies, Classifications, and Categories

Category Description	MOLDED CASE BREAKERS
Type	GFCI circuit breakers

Packaging

Carton	1
Weight Per each	0.5



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application

OtherGeneration - Conventional Energy - Conventional
EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine
Vessels and Equipment - Marine Vessels and Equipment -
OtherGeneration - Renewable Energy - Alternative Energy

standard

UL 489