



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



QBHW2045 45A 2P 22KA B BKR

Eaton Corp

Catalog Number	QBHW2045
Manufacturer	Eaton Corp
Description	Eaton QB Thermal Magnetic Circuit Breaker, Quicklag Industrial Thermal-Magnetic Circuit Breaker, 45 A, 22 Kaic, Two-Pole, 240 V, Non-Interchangeable, Q7, QBHW
Weight per unit	0.3000 (lbs/each)
Product Category	2 Pole Standard Trip Bolt-On

Features

dimensions	3.1000 IN X 2.0000 IN X 0.9000 IN
interrupt rating	22
Poles	2
Voltage Rating	120/240 V

Descriptions

Description	45A 2P 22KA B BKR
extra long description	ETN QBHW2045 2P 45A QBHW 22KA 240V
Features	Eaton has a wide selection of UL rated miniature circuit breakers for loadcenters, fuseboxes, or similar devices. Each pole provides steel frame calibration and arc chutes with 5 - 100A continuous in one-, two-, and three-pole designs. A full-range of accessories expand customization options, including various mounting and ring tung termination options.
Long Description	Eaton QB thermal magnetic circuit breaker,Quicklag industrial thermal-magnetic circuit breaker,45 A,22 kAIC,Two-pole,240 V,Non-Interchangeable,Q7,QBHW
Product Type	2P 45A QBHW 22KA 240V

Manufacturer Information

Brand	Eaton
GTIN	00786679152478
Manufacturers Part Number	QBHW2045
UPC	786679152478

Taxonomies, Classifications, and Categories

Category Description	PANELBOARD BRANCH BREAKERS
Type	Thermal magnetic circuit breakers

Packaging

Carton	1
Weight Per each	0.3



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	Generation - Conventional Energy - Conventional EnergyOtherGeneration - Renewable Energy - Alternative EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine Vessels and Equipment - Marine Vessels and Equipment - Other
standard	CSA Certified,UL Listed