

Specifications

Eaton QBHW3020H

Quicklag Industrial Thermal-Magnetic Circuit Breaker, Three-pole, 20A, 22 kAIC, 240V, Bolt-on



General specifications

PRODUCT NAME	Eaton QB thermal magnetic circuit breaker
CATALOG NUMBER	QBHW3020H
UPC	786679393208
PRODUCT LENGTH/DEPTH	3.8 in
PRODUCT HEIGHT	4.7 in
PRODUCT WIDTH	3.2 in
PRODUCT WEIGHT	1.1 lb
WARRANTY	1 year
CERTIFICATIONS	UL Listed CSA Certified
CATALOG NOTES	HACR rated



Powering Business Worldwide

Physical Attributes

CIRCUIT BREAKER TYPE	QBHW
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Three-pole
TYPE	Quicklag

Performance Ratings

AMPERAGE RATING	20 A
INTERRUPT RATING	22 kAIC
TRIP TYPE	Non-Interchangeable
VOLTAGE RATING	240 V - 240 V

Miscellaneous

QUANTITY	32
----------	----

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - QBHW3020H
-------------------------------	---

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



Specifications

Eaton QBHW3020H

Quicklag Industrial Thermal-Magnetic Circuit Breaker, Three-pole, 20A, 22 kAIC, 240V, Bolt-on



General specifications

PRODUCT NAME	Eaton QB thermal magnetic circuit breaker
CATALOG NUMBER	QBHW3020H
UPC	786679393208
PRODUCT LENGTH/DEPTH	3.8 in
PRODUCT HEIGHT	4.7 in
PRODUCT WIDTH	3.2 in
PRODUCT WEIGHT	1.1 lb
WARRANTY	1 year
CERTIFICATIONS	UL Listed CSA Certified
CATALOG NOTES	HACR rated



Powering Business Worldwide

Physical Attributes

CIRCUIT BREAKER TYPE	QBHW
MOUNTING METHOD	Bolt-on
NUMBER OF POLES	Three-pole
TYPE	Quicklag

Miscellaneous

QUANTITY	32
----------	----

Performance Ratings

AMPERAGE RATING	20 A
INTERRUPT RATING	22 kAIC
TRIP TYPE	Non-Interchangeable
VOLTAGE RATING	240 V - 240 V

Resources

SPECIFICATIONS AND DATASHEETS	Eaton Specification Sheet - QBHW3020H
-------------------------------	---

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

