



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



QBGFT1025 Type QB, 5MA GF Breaker 25A /1 Pole 120/240V, 10K *Eaton Corp*

Catalog Number	QBGFT1025
Manufacturer	Eaton Corp
Description	Eaton QB Gfci Circuit Breaker, Ground Fault Circuit Breaker, 25A, 10 Kaic, Single-Pole, 120/240V, Non-Interchangeable, 5 Ma Trip Sensitivity, QBGF
Weight per unit	0.5000 (lbs/each)
Product Category	On Circuit Breakers

Features

dimensions	1.0000 IN X 1.0000 IN X 1.0000 IN
interrupt rating	10
Poles	1
Voltage Rating	120/240 V

Descriptions

Description	TYPE QB, 5MA GF BREAKER 25A /1 POLE 120/240V, 10K
extra long description	ETN QBGFT1025 QB, 5MA GF 25A /1 POL
Features	Eaton has a wide selection of UL rated miniature circuit breakers for loadcenters, fuseboxes, or similar devices. Each pole provides steel frame calibration and arc chutes with 5 - 100A continuous in one-, two-, and three-pole designs. A full-range of accessories expand customization options, including various mounting and ring tung termination options.
Long Description	Eaton QB GFCI circuit breaker,Ground fault circuit breaker,25A,10 kAIC,Single-pole,120/240V,Non-Interchangeable,5 mA Trip sensitivity,QBGF
Product Type	QB, 5MA GF 25A /1 Pole 120/240V, 10kaic
Special Features	5 mA Trip Sensitivity

Manufacturer Information

Brand	Eaton
GTIN	00786680130977
Manufacturers Part Number	QBGFT1025
UPC	786680130977

Taxonomies, Classifications, and Categories

Category Description	MOLDED CASE BREAKERS
Type	GFCI circuit breakers



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.5

Uses, Certifications, and Standards

Application	OtherGeneration - Conventional Energy - Conventional EnergyDatacenters - IT Space: CI and Hyper ConvergedMarine Vessels and Equipment - Marine Vessels and Equipment - OtherGeneration - Renewable Energy - Alternative Energy
standard	UL 489