

Eaton QBHW3030H

Catalog Number: QBHW3030H

Quicklag Industrial Thermal-Magnetic Circuit Breaker, Three-pole, 30A, 22 kAIC, 240V, Bolt-on

General specifications



| | |
|---|-----------------------|
| Product Name | Catalog Number |
| Eaton QB thermal magnetic circuit breaker | QBHW3030H |
| | UPC |
| | 786679393307 |
| Product Length/Depth | Product Height |
| 3.8 in | 4.7 in |
| Product Width | Product Weight |
| 3.2 in | 1.1 lb |
| Warranty | Certifications |
| 1 year | CSA Certified |
| | UL Listed |
| Catalog Notes | |
| HACR rated | |

Physical Attributes

Circuit breaker type

QBHW

Mounting Method

Bolt-on

Number of poles

Three-pole

Type

Quicklag

Performance Ratings

Amperage Rating

30 A

Interrupt rating

22 kAIC

Trip Type

Non-Interchangeable

Voltage rating

240 V - 240 V

Miscellaneous

Quantity

32

Resources

Specifications and datasheets

[Eaton Specification Sheet - QBHW3030H](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton QBHW3030H

Catalog Number: QBHW3030H

Quicklag Industrial Thermal-Magnetic Circuit Breaker, Three-pole, 30A, 22 kAIC, 240V, Bolt-on

General specifications



| | |
|---|-----------------------|
| Product Name | Catalog Number |
| Eaton QB thermal magnetic circuit breaker | QBHW3030H |
| | UPC |
| | 786679393307 |
| Product Length/Depth | Product Height |
| 3.8 in | 4.7 in |
| Product Width | Product Weight |
| 3.2 in | 1.1 lb |
| Warranty | Certifications |
| 1 year | CSA Certified |
| | UL Listed |
| Catalog Notes | |
| HACR rated | |

Physical Attributes

Circuit breaker type

QBHW

Mounting Method

Bolt-on

Number of poles

Three-pole

Type

Quicklag

Performance Ratings

Amperage Rating

30 A

Interrupt rating

22 kAIC

Trip Type

Non-Interchangeable

Voltage rating

240 V - 240 V

Miscellaneous

Quantity

32

Resources

Specifications and datasheets

[Eaton Specification Sheet - QBHW3030H](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)