



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



QCD2060 Type QCD Breaker 2P 60A Din Rail Mounting 120/240V

Eaton Corp

Catalog Number	QCD2060
Manufacturer	Eaton Corp
Description	Eaton Quicklag Type QCD Industrial Thermal-Magnetic Circuit Breaker, Industrial Circuit Breaker, 60 A, 10 Kaic, Two-Pole, 120/240 V, Thermal-Magnetic, Cable-In/Cable-Out, QCD, Non-Interchangeable
Weight per unit	0.8800 (lbs/each)
Product Category	2 Pole Din Rail Mount Circuit

Features

connection	Cable-in/Cable-out
dimensions	4.0000 IN X 2.0000 IN X 3.0000 IN
interrupt rating	10
Poles	2
Voltage Rating	120/240 V

Descriptions

Description	TYPE QCD BREAKER 2P 60A DIN RAIL MOUNTING 120/240V
extra long description	ETN QCD2060 Eaton QC thermal magnet
Features	Eaton has a wide selection of UL rated miniature circuit breakers for loadcenters, fuseboxes, or similar devices. Each pole provides steel frame calibration and arc chutes with 5 - 100A continuous in one-, two-, and three-pole designs. A full-range of accessories expand customization options, including various mounting and ring tung termination options.
Long Description	Eaton Quicklag Type QCD Industrial Thermal-Magnetic Circuit Breaker, Industrial circuit breaker, 60 A, 10 kAIC, Two-pole, 120/240 V, Thermal-magnetic, Cable-in/cable-out, QCD, Non-interchangeable
Product Type	Eaton QC Thermal Magnetic Circuit Breaker

Manufacturer Information

Brand	Eaton
GTIN	00786679135969
Manufacturers Part Number	QCD2060
UPC	786679135969

Taxonomies, Classifications, and Categories

Category Description	Powerdefense Breakers
Type	Thermal magnetic circuit breakers

Availability

Status	Inactive
--------	----------



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Packaging

Carton	1
Weight Per each	0.88

Uses, Certifications, and Standards

Application	Generation - Conventional Energy - Conventional EnergyDatacenters - IT Space: CI and Hyper ConvergedOtherMarine Vessels and Equipment - Marine Vessels and Equipment - OtherGeneration - Renewable Energy - Alternative Energy
standard	UL Listed,CSA Certified