

Eaton R5A3040U

Catalog Number: R5A3040U

Eaton rotary disconnect switch, 40 A, Non-fusible, Three-pole, Rotary switch, R5 Series, 600 V



General specifications

Product Name

Eaton rotary disconnect switch

Catalog Number

R5A3040U

UPC

786685402888

Product Length/Depth

2.57 in

Product Height

3.35 in

Product Width

1.77 in

Product Weight

0.5 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

CCC Marked

Certifications

CSA Certified

EN Listed

IEC Rated

UL 508

Catalog Notes

Suitable as motor disconnect

Physical Attributes

Number of poles

Three-pole

Series

R5

Performance Ratings

Amperage Rating

40A

Voltage rating

600 V

Miscellaneous

Product Category

Rotary Switch

Resources

Brochures

[Pringle Switches - Bolted contact switches](#)

Multimedia

[Switching Devices Flex Center](#)

Specifications and datasheets

[Eaton Specification Sheet - R5A3040U](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

Eaton R5A3040U

Catalog Number: R5A3040U

Eaton rotary disconnect switch, 40 A, Non-fusible, Three-pole, Rotary switch, R5 Series, 600 V



General specifications

Product Name

Eaton rotary disconnect switch

Catalog Number

R5A3040U

UPC

786685402888

Product Length/Depth

2.57 in

Product Height

3.35 in

Product Width

1.77 in

Product Weight

0.5 lb

Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

Compliances

CCC Marked

Certifications

CSA Certified

EN Listed

IEC Rated

UL 508

Catalog Notes

Suitable as motor disconnect

Physical Attributes

Number of poles

Three-pole

Series

R5

Performance Ratings

Amperage Rating

40A

Voltage rating

600 V

Miscellaneous

Product Category

Rotary Switch

Resources

Brochures

[Pringle Switches - Bolted contact switches](#)

Multimedia

[Switching Devices Flex Center](#)

Specifications and datasheets

[Eaton Specification Sheet - R5A3040U](#)



Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2024 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)