

# Eaton R5A3040U

Catalog Number: R5A3040U

Eaton rotary disconnect switch, 40 A, Non-fusible, Three-pole, Rotary switch, R5 Series, 600 V

## General specifications



Photo is representative

### Product Name

Eaton rotary disconnect switch

### Catalog Number

R5A3040U

### UPC

786685402888

### Product Length/Depth

2.57 in

### Product Height

3.35 in

### Product Width

1.77 in

### Product Weight

0.5 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Compliances

CCC Marked

### Certifications

CSA Certified

EN Listed

IEC Rated

UL 508

### Catalog Notes

Suitable as motor disconnect

## Physical Attributes

### Number of poles

Three-pole

### Series

R5

## Performance Ratings

### Amperage Rating

40A

### Voltage rating

600 V

## Miscellaneous

### Product Category

Rotary Switch

## Resources

### Multimedia

[Switching Devices Flex Center](#)

### Specifications and datasheets

[Eaton Specification Sheet - R5A3040U](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)

# Eaton R5A3040U

Catalog Number: R5A3040U

Eaton rotary disconnect switch, 40 A, Non-fusible, Three-pole, Rotary switch, R5 Series, 600 V

## General specifications



Photo is representative

### Product Name

Eaton rotary disconnect switch

### Catalog Number

R5A3040U

### UPC

786685402888

### Product Length/Depth

2.57 in

### Product Height

3.35 in

### Product Width

1.77 in

### Product Weight

0.5 lb

### Warranty

Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.

### Compliances

CCC Marked

### Certifications

CSA Certified

EN Listed

IEC Rated

UL 508

### Catalog Notes

Suitable as motor disconnect

## Physical Attributes

### Number of poles

Three-pole

### Series

R5

## Performance Ratings

### Amperage Rating

40A

### Voltage rating

600 V

## Miscellaneous

### Product Category

Rotary Switch

## Resources

### Multimedia

[Switching Devices Flex Center](#)

### Specifications and datasheets

[Eaton Specification Sheet - R5A3040U](#)



Eaton Corporation plc  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.



[Eaton.com/socialmedia](https://www.eaton.com/socialmedia)