



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



RA4LS9FSD2W1EWH 4" Led Gimbal 27K/3K/35K/4K/5K D2W 600/900LM

Cooper Lighting Solutions

Catalog Number	RA4LS9FSD2W1EWH
Manufacturer	Cooper Lighting Solutions
Description	4-Inch Adjustable Recessed Led Retrofit Module, 600/900 Selectable Lumens, 90 Cri, 6-Color Field-Selectable 2700K, 3000K, 3500K, 4000K, 5000K, Dim-to-Warm, Matte White.
Weight per unit	0.9100 (lbs/each)
Product Category	Lighting

Features

Fixture Type	Retrofit Kit
Lamp Type	LED

Dimensions and Weight

Size	5.31 IN Length 3.46 IN Width 5.35 IN Height
------	---

Descriptions

Description	4" LED GIMBAL 27K/3K/35K/4K/5K D2W 600/900LM
extra long description	CLS RA4LS9FSD2W1EWH 4" RA, 600/900L
Long Description	4-inch adjustable recessed LED retrofit module, 600/900 selectable lumens, 90 CRI, 6-Color Field-Selectable 2700K, 3000K, 3500K, 4000K, 5000K, Dim-to-Warm, Matte White.
Product Type	4" Ra, 600/900LM, 5CCT, D2W, 120V, White
Special Features	RA4 4-inch Baffle Recessed Adjustable LED Trim suitable for new construction, remodel, and retrofit

Manufacturer Information

Brand	HALO
GTIN	00080083282975
Manufacturers Part Number	RA4LS9FSD2W1EWH
UPC	080083282975

Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	4" RA Retrofit Series

Packaging

Carton	1
Weight Per each	0.91



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	lighting
Mounting	Recessed
standard	Energy Star Certified; IECC Compliant; Title 24 Compliant; UL Listed; RoHS Compliant; IC Rated