



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



RA6LS9FSD2W1EWHD 6" Led Gimbal DM 27K/3K/35K/4K/5K D2W Lumen SLCT *Cooper Lighting Solutions*

Catalog Number	RA6LS9FSD2W1EWHD
Manufacturer	Cooper Lighting Solutions
Description	6-Inch Adjustable Recessed Led Retrofit Module, 600/900 Selectable Lumens, 6-Color Selectable CCT Plus Dim to Warm Option, 120V 60 HZ, Le & Te Phase Cut 5% Dimming, Matte White.
Weight per unit	2.7 (lbs/each)
Product Category	Lighting

Features

amperage rating	0.07A at 120V
Lamp Type	LED
Voltage Rating	120V
Wattage	9.5 W

Material, Color, and Finish

Finish	Matte White
Style	(blank)

Descriptions

Description	6" LED GIMBAL DM 27K/3K/35K/4K/5K D2W LUMEN SLCT
extra long description	CLS RA6LS9FSD2W1EWHDM 6" RA, 600/10
Long Description	6-inch adjustable recessed LED retrofit module, 600/900 selectable lumens, 6-color selectable CCT plus dim to warm option, 120V 60 Hz, LE & TE phase cut 5% dimming, Matte White.
Product Type	6" Ra, 600/1000LM, 5CCT, D2W, 120V, DM
Special Features	Round 4" & 6" Adjustable Canless LED Downlights suitable for remodel and new construction installations (For new construction, use with canless mounting frames/plates)

Manufacturer Information

Brand	HALO
GTIN	00080083283033
Manufacturers Part Number	RA6LS9FSD2W1EWHDM
UPC	080083283033

Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	4" RA Retrofit Series

Packaging

Carton	1
Weight Per each	2.73



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

Application	lighting
Mounting	Recessed
standard	Energy Star Certified; IECC Compliant; Title 24 Compliant; UL Listed; RoHS Compliant; IC Rated