

# Eaton RDCH42B200I

Catalog Number: RDCH42B200I

Eaton CH 3/4-inch Loadcenter Retrofit Stacking Kit, Main circuit breaker, 200 A, Retro size group d, Cover height: 47 in, Cover width: 24 in, NEMA 1, 25 kAIC, CH, Surface, flush, 42 Circuits, Single-phase, 0.75 in, #1 AWG-300 kcmil

## General specifications



Photo is representative

### Product Name

Eaton CH retrofit kit

### UPC

786685211114

### Product Height

45 in

### Product Weight

1 lb

### Certifications

UL 67

### Catalog Number

RDCH42B200I

### Product Length/Depth

6 in

### Product Width

22 in

### Warranty

1 year

### Catalog Notes

Specific cover sizes are available. Be sure to specify the custom cover option and provide exact dimensions required.

## Product specifications

### Type

Retrofit kit

### Amperage Rating

200 A

### Main circuit breaker

CH

### Mounting

Surface, flush

### Number of circuits

42

### Phase

Single-phase

### Wire size

#1 AWG-300 kcmil

### Box size

Retro size group d

### Cover height

47

### Cover width

24

### Enclosure

NEMA 1

### Interrupt rating

25 kAIC

## Resources

### Multimedia

[AFCI Educational Video](#)

### Specifications and datasheets

[Eaton Specification Sheet - RDCH42B200I](#)

### Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)

# Eaton RDCH42B200I

Catalog Number: RDCH42B200I

Eaton CH 3/4-inch Loadcenter Retrofit Stacking Kit, Main circuit breaker, 200 A, Retro size group d, Cover height: 47 in, Cover width: 24 in, NEMA 1, 25 kAIC, CH, Surface, flush, 42 Circuits, Single-phase, 0.75 in, #1 AWG-300 kcmil

## General specifications



Photo is representative

### Product Name

Eaton CH retrofit kit

### UPC

786685211114

### Product Height

45 in

### Product Weight

1 lb

### Certifications

UL 67

### Catalog Number

RDCH42B200I

### Product Length/Depth

6 in

### Product Width

22 in

### Warranty

1 year

### Catalog Notes

Specific cover sizes are available. Be sure to specify the custom cover option and provide exact dimensions required.

## Product specifications

### Type

Retrofit kit

### Amperage Rating

200 A

### Main circuit breaker

CH

### Mounting

Surface, flush

### Number of circuits

42

### Phase

Single-phase

### Wire size

#1 AWG-300 kcmil

### Box size

Retro size group d

### Cover height

47

### Cover width

24

### Enclosure

NEMA 1

### Interrupt rating

25 kAIC

## Resources

### Multimedia

[AFCI Educational Video](#)

### Specifications and datasheets

[Eaton Specification Sheet - RDCH42B200I](#)

### Warranty guides

[Eaton type CH circuit breaker limited warranty June 2024](#)