

# Specifications

## Eaton RES-60

Eaton Bussmann series RES fuse, time lag, non current-limiting, Industrial and commercial structures, 60 A, Class H, Non-indicating, Ferrule end x ferrule end, 10 kAIC at 250 Vac, Standard, 10, 600 V



### General specifications

PRODUCT NAME	Eaton Bussmann series RES fuse
CATALOG NUMBER	RES-60
UPC	051712110600
EAN	5027590465991
PRODUCT LENGTH/DEPTH	0.78 in
PRODUCT HEIGHT	5.5 in
PRODUCT WIDTH	0.78 in
PRODUCT WEIGHT	0.29 lb
WARRANTY	Not Applicable
COMPLIANCES	Not Applicable

## Electrical rating

AMPERAGE RATING	60 A
INTERRUPT RATING	10 kAIC at 250 Vac
VOLTAGE RATING	600 V

## General information

CLASS	Class H
CONNECTION	Ferrule end x ferrule end
FUSE INDICATOR	Non-indicating
QUANTITY	10
SPECIAL FEATURES	Super lag, time lag, non current-limiting

## Physical details

PACKAGING TYPE	Standard
----------------	----------

## Resources

CATALOGS	<a href="#">Bussmann series complete full line catalog no. 1007</a>
	<a href="#">RES-60~SUPER LAG RENEWABLE FUSE 60/600</a>
	<a href="#">Edison full line catalog 1005</a>
MULTIMEDIA	<a href="#">Bussmann series Fuseology</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - RES-60</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications

## Eaton RES-60

Eaton Bussmann series RES fuse, time lag, non current-limiting, Industrial and commercial structures, 60 A, Class H, Non-indicating, Ferrule end x ferrule end, 10 kAIC at 250 Vac, Standard, 10, 600 V



### General specifications

PRODUCT NAME	Eaton Bussmann series RES fuse
CATALOG NUMBER	RES-60
UPC	051712110600
EAN	5027590465991
PRODUCT LENGTH/DEPTH	0.78 in
PRODUCT HEIGHT	5.5 in
PRODUCT WIDTH	0.78 in
PRODUCT WEIGHT	0.29 lb
WARRANTY	Not Applicable
COMPLIANCES	Not Applicable

## Electrical rating

AMPERAGE RATING	60 A
INTERRUPT RATING	10 kAIC at 250 Vac
VOLTAGE RATING	600 V

## General information

CLASS	Class H
CONNECTION	Ferrule end x ferrule end
FUSE INDICATOR	Non-indicating
QUANTITY	10
SPECIAL FEATURES	Super lag, time lag, non current-limiting

## Physical details

PACKAGING TYPE	Standard
----------------	----------

## Resources

CATALOGS	<a href="#">Bussmann series complete full line catalog no. 1007</a>
	<a href="#">RES-60~SUPER LAG RENEWABLE FUSE 60/600</a>
	<a href="#">Edison full line catalog 1005</a>
MULTIMEDIA	<a href="#">Bussmann series Fuseology</a>
SPECIFICATIONS AND DATASHEETS	<a href="#">Eaton Specification Sheet - RES-60</a>

PROJECT NAME:

PROJECT NUMBER:

PREPARED BY:

DATE:



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

