



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



RI06PV Dimmer Rotary SP/3W 600W 120V Pset Iv

Eaton Wiring Devices

Catalog Number	RI06PV
Manufacturer	Eaton Wiring Devices
Description	Eaton Rotary Dimmer, Power Failure Memory, With Preset, #16 Awg, 5A, 120V, Wire Lead, Maintained Closure, Ivory, Indoor, 60 HZ, Incandescent, Halogen, 0° to 40°C, Single-Pole, Three-Way, Polycarbonate, 600W
Weight per unit	0.0010 (lbs/each)
Product Category	Lighting Dimmers

Features

amperage rating	5
dimensions	2.3000 IN X 3.0600 IN X 4.7500 IN
load	INCHAL
Material	Polycarbonate
Mounting Type	Flush Mount
Voltage Rating	120 V

Descriptions

Description	DIMMER ROTARY SP/3W 600W 120V PSET IV
extra long description	EWD RI06P-V Dimmer Rotary SP/3W 600
Features	Bring the right ambiance to the room and save energy at the same time. Lighting controls reduce the amount of electricity used by your lights by controlling power loads at the switch, which saves electricity, reduces utility bills and extends the life of the bulb. Eaton's lighting control dimmers are compatible with most common lighting loads, including LED, CFL, MLV, ELV and Fluorescent. Available in multiple styles and colors, you can select the perfect dimmer for every room in your home or commercial bu
Long Description	Eaton rotary dimmer, Power failure memory, with preset, #16 AWG, 5A, 120V, Wire lead, Maintained closure, Ivory, Indoor, 60 Hz, Incandescent, halogen, 0° to 40°C, Single-pole, three-way, Polycarbonate, 600W
Product Type	Dimmer Rotary SP/3W 600W 120V Pset Iv
Special Features	Power failure memory, with preset

Manufacturer Information

Brand	Eaton Wiring Devices
GTIN	00032664699016
Manufacturers Part Number	RI06P-V
UPC	032664699016



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	Rotary dimmer

Packaging

Carton	10
Package	100
Weight Per each	0.001

Uses, Certifications, and Standards

Application	Residential Bldgs & Facilities - Residential Bldgs & Facilities - Other
environmental conditions	Indoor
Frequency Rating	60 Hz
Mounting	FLUSH
Operating Temperature standard	0 to 40 °C cULus Listed,NOM