



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **RKIT35PS2AG44850 4' Linear Retro Kit 50K LM Adj 4000L-5000L-6000L** *Keystone Technologies*

Catalog Number	RKIT35PS2AG44850
Manufacturer	Keystone Technologies
Description	Linear Led Retrofit Kit, 5000K, 120-277V Input, 0-10V Dimming, Power Selectable Between 23W, 29W, and 35W, Includes (2) 44IN Alumagroove Modules, (2) 44IN Lenses, (1) Led Driver, and (1) Bag Of Assorted Mounting Hardware
Weight per unit	1.8 (lbs/each)
Product Category	Lighting

### **Features**

Ballast Type	N/A
beam angle	N/A
Circuit Type	N/A
Input Voltage	120-277V
ip rating	N/A
lumens	N/A
Nominal Length	N/A
Nominal Size	4' Linear
Number of Lamps	N/A
Output Current	N/A
Output Voltage	N/A
Sensor Type	N/A
Wattage	N/A
Wire Type	N/A

### **Material, Color, and Finish**

Base Type	N/A
color rendering index (cri)	>80 Deg
color temperature	5000
housing color	N/A

### **Descriptions**

Construction	N/A
Description	4' LINEAR RETRO KIT 50K LM ADJ 4000L-5000L-6000L
extra long description	Key KT-RKIT35PS-2AG44-850-VDIM 36W,
Long Description	Linear LED Retrofit Kit, 5000K, 120-277V Input, 0-10V Dimming, Power Selectable between 23W, 29W, and 35W, Includes (2) 44in Alumagroove Modules, (2) 44in Lenses, (1) LED Driver, and (1) bag of assorted mounting hardware
Product Type	36W, 2X2' Linear Led Kit, 4000 Lumens, 0-10V Dimming- Indivi



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Manufacturer Information

Brand	Keystone
GTIN	00843654128160
Manufacturers Part Number	KT-RKIT35PS-2AG44-850-VDIM
UPC	843654128160

## Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
----------------------	--

## Packaging

Carton	1
Package	20
Weight Per each	1.8

## Uses, Certifications, and Standards

Energy Star	N
-------------	---