



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



RHDH163PTC Radiant Dehum Fan Speed CTRL 1.6A Tri-Color

Pass & Seymour/Legrand

Catalog Number	RHDH163PTC
Manufacturer	Pass & Seymour/Legrand
Description	Upgrade Your Fan Control With The Sweet Sound Of Silence. Specially Designed to Virtually Eliminate The Fan Motor "Hum." This Device Provides Quieter Fan Speed Control While Featuring The Sleek, Clean Lines Of Radiant® For A Sophisticated Touch. This Fan Control Switch Handles A Max Load Of 1.6A. Made Exclusively For Use With Screwless Wall Plates From The Radiant® Collection, Sold Separately.
Weight per unit	0.3000 (lbs/each)
Product Category	Fan Speed Switches & Controls

Features

amperage rating	1.6
connection	Back Wired
Contact Rating	120VAC
media	Yes
Mounting Type	Box
Number of Gangs	1.0
Number of Switches	1.0
Poles	1, 3-Way
Switch Type	Paddle
Voltage	120.0 V
Voltage Rating	120
Wire Size	#14 - #10 Awg

Material, Color, and Finish

Color	Ivory, Light Almond, White
Finish	Matte

Dimensions and Weight

Size	Depth 1.25" x Width 1.75" x Height 4.25"
------	--



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Descriptions

Description	RADIANT DEHUM FAN SPEED CTRL 1.6A TRI-COLOR
extra long description	P&S RHDH163PTC RADIANT DEHUM FAN SP
Features	Fan Control
Long Description	Upgrade your fan control with the sweet sound of silence. Specially designed to virtually eliminate the fan motor "hum." This device provides quieter fan speed control while featuring the sleek, clean lines of radiant® for a sophisticated touch. This fan control switch handles a max load of 1.6A. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.
Product Type	Radiant Dehum Fan Speed CTRL 1.6A, Tri
Special Features	This fan control offers a specially designed capacitive circuitry de-hummer feature that virtually eliminates fan motor "hum" for quiet fan speed control.

Manufacturer Information

Brand	LEGRAND-PASS & SEYMOUR
GTIN	00785007053418
Manufacturers Part Number	RHDH163PTC
UPC	785007053418

Taxonomies, Classifications, and Categories

Category Description	Residential dimmers, motion sensors, controls, & photo cells
Type	SWITCH

Trade Size

Amperage	15.0
----------	------

Packaging

Carton	1
Package	24
Weight Per each	0.3

Uses, Certifications, and Standards

Application	Residential
Enclosure	Thermoplastic
environmental conditions	Indoor Only
Mounting	WALL
Operating Temperature	0°C to 40°C
standard	CULUS, UL, CSA Listed, cULus, UL Listed