



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## RL4069WZRGBWWHR 4" 7W Led Retro Baffle-Trim 22K-65K RGB Wizpro

*Cooper Lighting Solutions*

Catalog Number	RL4069WZRGBWWHR
Manufacturer	Cooper Lighting Solutions
Description	4" Smart Wi-Fi Recessed Led Trim, Wiz Pro Enabled (Wi-Fi + Bluetooth), 600 Lumens, 90 Cri (Min), Full Color, Tunable White (2200K - 6500K), Matte White Baffle Trim, Retrofit, Recyclable Packaging
Weight per unit	0.5400 (lbs/each)
Product Category	Lighting

### Features

amperage rating	0.05A at 120V
Lamp Type	LED
Socket Type	N/A
Voltage Rating	120V
Wattage	7.1W

### Material, Color, and Finish

Finish	Matte White, White Baffle
Style	(blank)

### Descriptions

Description	4" 7W LED RETRO BAFFLE-TRIM 22K-65K RGB WIZPRO
extra long description	CLS RL4069WZRGBWWHR RL4" 600LM, WIZ
Long Description	4" Smart Wi-Fi Recessed LED Trim, WiZ Pro enabled (Wi-Fi + Bluetooth), 600 lumens, 90 CRI (min), Full Color, Tunable White (2200K - 6500K), Matte white baffle trim, Retrofit, Recyclable packaging
Product Type	RL4" 600LM, Wiz Pro RGBW, 120V, WH
Special Features	Create the perfect mood with millions of colors and warm-to-cool tunable whites (2200K-6500K)

### Manufacturer Information

Brand	HALO
GTIN	00080083256167
Manufacturers Part Number	RL4069WZRGBWWHR
UPC	080083256167

### Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	RL4 LED



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Packaging

Carton	1
Package	4
Weight Per each	0.54

## Uses, Certifications, and Standards

Application	lighting
Mounting standard	Recessed ENERGY STAR Qualified;IECC Compliant;California Title 20;Title 24 Compliant;RoHS Compliant;Wet Locations;AIR-TITE (TM) Certified ASTM E283;LM79 and/or LM80 Tested