



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## RL460WH930 4" Led Retro 30K 90CRI WHT *Cooper Lighting Solutions*

Catalog Number	RL460WH930
Manufacturer	Cooper Lighting Solutions
Description	00080083690770 0080083 080083690770 08008369077 69077 RL460WH930 RL4 WH 90CRI 3000K PK, HV Cooper Lighting RL460WH930PK CooperLighting RL460WH930PK Eaton / Cooper Lighting RL460WH930PK Eaton Cooper Lighting RL460WH930PK Eaton Cooper Lighting RL460WH930PK HALO - Cooper Lighting RL460WH930PK HALO - Recessed RL460WH930PK
Weight per unit	1.1 (lbs/each)
Product Category	Led Recessed Architectural & S

### Features

amperage rating	0.075A - 0.0875A (at 120V)
Lamp Type	LED
Voltage Rating	120
Wattage	8 W

### Descriptions

Long Description	00080083690770 0080083 080083690770 08008369077 69077 RL460WH930 RL4 WH 90CRI 3000K PK, HV Cooper Lighting RL460WH930PK CooperLighting RL460WH930PK Eaton / Cooper Lighting RL460WH930PK Eaton Cooper Lighting RL460WH930PK Eaton Cooper Lighting RL460WH930PK HALO - COOPER LIGHTING RL460WH930PK HALO - Recessed RL460WH930PK
Product Type	Halo RL4 WH 90CRI 3000K PK, HV
Special Features	ENERGY STAR® certified

### Manufacturer Information

Brand	HALO - RECESSED
GTIN	00080083690770
Manufacturers Part Number	RL460WH930PK
sub brand	RL4 All-Purpose LED Baffle-trim Modules
UPC	080083690770

### Taxonomies, Classifications, and Categories

Category Description	LED GENERAL PURPOSE LIGHTING
Type	RL4 LED



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Availability

Manufacturer Status ..... Inactive

Status ..... Inactive

## Packaging

Carton ..... 1

Weight Per each ..... 1.1299

## Uses, Certifications, and Standards

Application ..... lighting

standard ..... UL/cUL Listed 1598 Luminaire;UL Classified;cULus Listed - Damp Location;cULus Listed - Wet Location;IP65 Rated;Energy Star Certified;AIR-TITE (TM) Certified ASTM E28;California Title 24;Title 20 Compliant;IECC Compliant;EMI/RFI per FCC 47CFR Part 15 B;RoHS Compliant