

# Specifications



## Eaton RJDN250

Eaton enclosed circuit breaker, Enclosure, 125-250A, Series C, NEMA 3R, JD, JDB, HJD, JDC, Surface

### General specifications

<b>PRODUCT NAME</b>	Eaton enclosed circuit breaker
<b>CATALOG NUMBER</b>	RJDN250
<b>UPC</b>	786679256145
<b>PRODUCT LENGTH/DEPTH</b>	10.22 in
<b>PRODUCT HEIGHT</b>	37.5 in
<b>PRODUCT WIDTH</b>	11.88 in
<b>PRODUCT WEIGHT</b>	37 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed CSA Certified
<b>CATALOG NOTES</b>	With Knockouts

## Product specifications

<b>TYPE</b>	Circuit Breaker Enclosure
<b>AMPERAGE RATING</b>	125-250A
<b>CIRCUIT BREAKER TYPE</b>	JD, JDB, HJD, JDC
<b>ENCLOSURE</b>	NEMA 3R
<b>SERIES</b>	Series C
<b>MOUNTING METHOD</b>	Surface mounting

## Resources

<b>CATALOGS</b>	<a href="#">Circuit Protection, Molded Case Circuit Breakers, Volume 4, Tab 2</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - RJDN250</a>

---

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**

---



**Eaton Corporation plc**

Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.



# Specifications



## Eaton RJDN250

Eaton enclosed circuit breaker, Enclosure, 125-250A, Series C, NEMA 3R, JD, JDB, HJD, JDC, Surface

### General specifications

<b>PRODUCT NAME</b>	Eaton enclosed circuit breaker
<b>CATALOG NUMBER</b>	RJDN250
<b>UPC</b>	786679256145
<b>PRODUCT LENGTH/DEPTH</b>	10.22 in
<b>PRODUCT HEIGHT</b>	37.5 in
<b>PRODUCT WIDTH</b>	11.88 in
<b>PRODUCT WEIGHT</b>	37 lb
<b>WARRANTY</b>	Eaton Selling Policy 25-000, one (1) year from the date of installation of the Product or eighteen (18) months from the date of shipment of the Product, whichever occurs first.
<b>CERTIFICATIONS</b>	UL Listed CSA Certified
<b>CATALOG NOTES</b>	With Knockouts

## Product specifications

<b>TYPE</b>	Circuit Breaker Enclosure
<b>AMPERAGE RATING</b>	125-250A
<b>CIRCUIT BREAKER TYPE</b>	JD, JDB, HJD, JDC
<b>ENCLOSURE</b>	NEMA 3R
<b>SERIES</b>	Series C
<b>MOUNTING METHOD</b>	Surface mounting

## Resources

<b>CATALOGS</b>	<a href="#">Circuit Protection, Molded Case Circuit Breakers, Volume 4, Tab 2</a>
<b>SPECIFICATIONS AND DATASHEETS</b>	<a href="#">Eaton Specification Sheet - RJDN250</a>

---

**PROJECT NAME:**

**PROJECT NUMBER:**

**PREPARED BY:**

**DATE:**

---



**Eaton Corporation plc**  
Eaton House  
30 Pembroke Road  
Dublin 4, Ireland  
Eaton.com

© 2025 Eaton. All Rights Reserved.

Eaton is a registered trademark. Follow us on social media to get the latest product and support information.  
All other trademarks are property of their respective owners.

