



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



RL6069FSD2W1EWH 6" Led Trim 27K/3K/35K/4K/5K D2W Dim Dir MNT 600LM *Cooper Lighting Solutions*

| | |
|------------------|--|
| Catalog Number | RL6069FSD2W1EWH |
| Manufacturer | Cooper Lighting Solutions |
| Description | 5/6-Inch Recessed Led Retrofit Module, 600 Lumens, 90 Cri, Selectable CCT With D2W Option, 120V 60HZ, Le & Te Phase Cut 5% Dimming Driver, Matte White Flange. |
| Weight per unit | 1.6 (lbs/each) |
| Product Category | Lighting |

Features

| | |
|--------------|--------------|
| Fixture Type | Retrofit Kit |
| Lamp Type | LED |

Dimensions and Weight

| | |
|------|---|
| Size | 7.48 IN Length 3.35 IN Width 7.99 IN Height |
|------|---|

Descriptions

| | |
|------------------------|--|
| Description | 6" LED TRIM 27K/3K/35K/4K/5K D2W DIM DIR MNT 600LM |
| extra long description | CLS RL56069FSD2W1EWH 5/6" RL, 600LM |
| Long Description | 5/6-inch recessed LED retrofit module, 600 lumens, 90 CRI, selectable CCT with D2W option, 120V 60Hz, LE & TE phase cut 5% dimming driver, matte white flange. |
| Product Type | 5/6" RL, 600LM, 5CCT, D2W, 120V |
| Special Features | Available in 4" and 6" |

Manufacturer Information

| | |
|---------------------------|-------------------|
| Brand | HALO |
| GTIN | 00080083258925 |
| Manufacturers Part Number | RL6069FSD2W1EWHDM |
| UPC | 080083258925 |

Taxonomies, Classifications, and Categories

| | |
|----------------------|--|
| Category Description | LED ARCHITECTURAL & SPECIFICATION LIGHTING |
| Type | RL56 LED |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 4 |
| Weight Per each | 1.63 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Uses, Certifications, and Standards

| | |
|-------------|--|
| Application | lighting |
| Mounting | Recessed |
| standard | RoHS Compliant;Energy Star;California Title 20;California Title 24;IECC Compliant;UL Listed;IC Rated |