



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## RS1 8.5"X8.5"X4" Junction Box *Crouse-Hinds*

Catalog Number	RS1
Manufacturer	Crouse-Hinds
Description	Eaton Crouse-Hinds Series RS Junction Box, 8-1/2" X 8-1/2" X 4", Feraloy Iron Alloy, Surface Mount
Weight per unit	19.0 (lbs/each)
Product Category	Cast Boxes

### Features

dimensions	8.5000 IN X 4.0000 IN X 8.5000 IN
Material	FERALOY IRON ALLOY

### Dimensions and Weight

Size	8-1/2 In X 8-1/2 In X 4 In
------	----------------------------

### Descriptions

Construction	Raintight
Description	8.5"X8.5"X4" JUNCTION BOX
extra long description	CRS-H RS1 8 1/2 X 8 1/2 X 4 JUNC BX
Features	Crouse-Hinds series RS, RSM and RSS junction boxes are installed in conduit systems to act as pull boxes for conductors, provide openings and space for making splices and taps in conductors, provide for branch conduit runs, and provide access to conductors for maintenance and future system changes. RS, RSM and RSS junction boxes are designed with configurable conduit hub plates, permitting a wide range of hub arrangements and sizes.
Long Description	Eaton Crouse-Hinds series RS junction box, 8-1/2" x 8-1/2" x 4", Feraloy iron alloy, Surface mount
Product Type	8 1/2 X 8 1/2 X 4 Junc BX Gasks & Bolts
Special Features	Two Gang, With Gasket

### Manufacturer Information

Brand	EATON CROUSE-HINDS SERIES
GTIN	00782274595801
UPC	782274595801

### Taxonomies, Classifications, and Categories

Category Description	HUB STYLE BOXES (GUAB, GUAT, ETC)
Type	JUNCTION BOX

### Packaging

Carton	1
Weight Per each	19



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

---

## Uses, Certifications, and Standards

Application	Ind Facilities & Factories - Facility: Power Distribution and Control
standard	UL 514B, CSA C22.2