



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **S10N04P16P 1.5KVA Buck Boost Transformer 1PH 120X240-12/24V**

*Eaton Corp*

Catalog Number	S10N04P16P
Manufacturer	Eaton Corp
Description	Eaton General-Purpose Encapsulated Transformer, Ep, Single-Phase, PV: 120 X 240V, Taps: None, SV: 12/24V, 115°C, 1.5 Kva, Al Windings, Frame: 67P, Indoor-Outdoor.
Weight per unit	40.0 (lbs/each)
Product Category	Single Phase Non Ventilated to

### **Features**

connection	3B
design	EP
dimensions	6.5600 IN X 5.5300 IN X 13.0300 IN
frame	67P
Number of Phases	Single-phase
Primary Voltage	120 V, 240 V
Secondary Voltage	12/24 V

### **Descriptions**

Description	1.5KVA BUCK BOOST TRANSFORMER 1PH 120X240-12/24V
extra long description	ETN S10N04P16P 1.5KVA BUCK BOOST TX
Features	Eaton's EP (single-phase) and EPT (three-phase) general purpose encapsulated dry-type transformers are of the two-winding type, encapsulated (potted) in a mix of epoxy coated sand and gravel, and are available in a wide variety of primary and secondary voltage combinations. General purpose encapsulated transformers are designed, manufactured and tested in accordance with all of the latest applicable ANSI, NEMA and IEEE standards, and are designed for continuous operation at rated kVA.
Long Description	Eaton General-Purpose Encapsulated Transformer, EP, Single-phase, PV: 120 X 240V, Taps: None, SV: 12/24V, 115°C, 1.5 kVA, Al windings, Frame: 67P, Indoor-Outdoor.
Product Type	1.5KVA Buck Boost TX 1PH 120X240-12/24V

### **Manufacturer Information**

Brand	Eaton
GTIN	00786680073564
Manufacturers Part Number	S10N04P16P
UPC	786680073564



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	BUCK & BOOST TRANSFORMERS
Type	Encapsulated transformer

## Packaging

Carton	1
Weight Per each	40

## Uses, Certifications, and Standards

Application	Commercial / Institutional Buildings / Structures - Commercial / Institutional Buildings / Structures - Other
Frequency Rating	60 Hz
standard	UL Listed
Temperature Rating	115 °C rise