



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## S11258 Wi-Fi 15W Led Par 38 RGB/Tunable Flood

Satco

Catalog Number	S11258
Manufacturer	Satco
Description	15 Watt - PAR38 Led Lamp - RGB and Tunable White - Starfish lot - 120 Volts - 1200 Lumens
Weight per unit	1.2 (lbs/each)
Product Category	Lighting

### Features

average life	25000
Base	Medium
beam angle	40
lumens	1.2k
Material	Plastic
Shape	PAR38
Warranty	3 Year Limited - 3 hr per day

### Material, Color, and Finish

color temperature	5000
Finish	white

### Dimensions and Weight

Size	5
------	---

### Descriptions

Description	WI-FI 15W LED PAR 38 RGB/TUNABLE FLOOD
extra long description	SATCO S11258 15PAR38/LED/RGB/TW/SF
Long Description	15 Watt - PAR38 LED Lamp - RGB and Tunable White - Starfish IOT - 120 Volts - 1200 Lumens
Product Type	15PAR38/Led/RGB/TW/SF
Special Features	Unavailable for sale in California ; Color temperature: Warm to Natural Light/Color Changeable ; Dimmable Only with Starfish App ; IoT enabled ; Actual watts: 15W ; Energy Star: Yes ; Warranty: 3 Year Limited - 3 hr per day ; Incandescent Equivalent: 90W ; Indoor/Outdoor: Indoor and Outdoor ; Material: Plastic ; Enclosed fixture rated: Yes ; Location rating: Wet ; Voice assistants supported: Siri - Alexa - Hey Google - SmartThings

### Manufacturer Information

Brand	Satco
GTIN	00045923112584
Manufacturers Part Number	S11258
UPC	045923112584



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description LED PAR SHAPE LAMPS

Type LED PAR

## Packaging

Carton 1

Weight 0.33

Weight Per each 1.21

## Uses, Certifications, and Standards

Operating Temperature -20C (-4F) to a maximum of +40C (+104F)

standard cULus