



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## S11851 6" 15W Led Commercial DNLTL 27K/3K/35K/4K/5K 1600L

Satco

Catalog Number	S11851
Manufacturer	Satco
Description	15-Watt Commercial Led Downlight - 6 In. - CCT Adjustable - 120-277 Volts - Econo
Weight per unit	1.1 (lbs/each)
Product Category	Lighting

### Features

average life	50000
Base	Integrated LED
beam angle	90

### Material, Color, and Finish

Finish	white
--------	-------

### Dimensions and Weight

Size	H:3.00 D:7.40
------	---------------

### Descriptions

Description	6" 15W LED COMMERCIAL DNLTL 27K/3K/35K/4K/5K 1600L
extra long description	SATCO S11851 15WLED/CDL/6/CCT/120-2
Long Description	15-Watt Commercial LED Downlight - 6 in. - CCT Adjustable - 120-277 Volts - Econo
Product Type	15WLED/CDL/6/CCT/120-277
Special Features	Lawful for sale in California ; Lumens: 1600 ; CCT: 2700K/3000K/3500K/4000K/5000K ; Color Temperature: Warm to Cool White ; Dimmable: Yes-Dimmable ; Dimmable Text: 0-10V Dimming Only ; Includes: 18-inch whip ; DLC Approved: No ; Energy Star: Yes ; Warranty: 5 Year Limited - Fixtures ; ADA Compliant: Yes ; Air Tight: Yes ; IC Rated: Yes ; Amps: 0.140A ; CCT Selectable: Yes ; FCC Compliant: Yes ; CFL Equivalent: 26W ; Indoor/Outdoor: Indoor and Outdoor ; Lens Finish: Plastic ; Lens Material: Polycarbonate (P)

### Manufacturer Information

Brand	Satco
GTIN	00045923118517
Manufacturers Part Number	S11851
UPC	045923118517



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Taxonomies, Classifications, and Categories

Category Description	LED ARCHITECTURAL & SPECIFICATION LIGHTING
Type	RECESSED

## Packaging

Carton	1
Package	8
Weight Per each	1.05

## Uses, Certifications, and Standards

standard	cETLus - Listed
----------	-----------------