
4 INCH ROUND CEILING BOX

S120HAC | [Pass & Seymour](#)



FEATURES & BENEFITS

4" Round Ceiling Box with a bar hanger that adjusts to 16" or 24" joist spacing. It has four Auto/Clamps. It is constructed with impact-resistant Noryl thermoplastic, making it virtually unbreakable and non-conductive. Its depth-mounting gauge at bottom of bracket helps you align the box at the proper depth relative to the ceiling. 50 pack.



- Auto/Clamp cable clamps molded in, hold wire securely in box.
- UL Listed for fixture support -- max weight rating 50 lbs.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Size: 4"

Type: Ceiling Box

Special Features: Round

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: No

CUL Listing No: No

cULus: No

cURus: No

Federal Spec: No

UL Listing No: Yes

UN SPSC: 39121308

UR: No

DIMENSIONS

Depth (US): 2.1875

Diameter (US): 4"

Volume: 20.25

TECHNICAL INFORMATION

Material: Plastic

Mounting: Hanger bar & bracket

Shape: round

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Buy American Act Compliant



4 INCH ROUND CEILING BOX

S120HAC | [Pass & Seymour](#)



FEATURES & BENEFITS

4" Round Ceiling Box with a bar hanger that adjusts to 16" or 24" joist spacing. It has four Auto/Clamps. It is constructed with impact-resistant Noryl thermoplastic, making it virtually unbreakable and non-conductive. Its depth-mounting gauge at bottom of bracket helps you align the box at the proper depth relative to the ceiling. 50 pack.



- Auto/Clamp cable clamps molded in, hold wire securely in box.
- UL Listed for fixture support -- max weight rating 50 lbs.
- For covering patents, see www.legrand.us/patents.

SPECIFICATIONS

GENERAL INFO

Size: 4"

Type: Ceiling Box

Special Features: Round

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: No

CUL Listing No: No

cULus: No

cURus: No

Federal Spec: No

UL Listing No: Yes

UN SPSC: 39121308

UR: No

DIMENSIONS

Depth (US): 2.1875

Diameter (US): 4"

Volume: 20.25

TECHNICAL INFORMATION

Material: Plastic

Mounting: Hanger bar & bracket

Shape: round

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA

Buy American Act Status: Buy American Act Compliant

