



## SWITCH & OUTLET BOX

S122R | [Pass & Seymour](#)

### FEATURES & BENEFITS

Durable, impact-resistant thermoplastic boxes complemented by innovative extras that cut installation time. Single Gang, Deep Switch and Outlet Box. Extra deep for dimmers, GFCIs and thermostats, yet suitable for 2x4 construction. Two Quick/Click Entries, 100 Pack.



- Quick/Click feature secures devices quickly and easily.
- Does not strip when over-torqued.
- Durable, impact-resistant thermoplastic box.
- Innovative extras that cut installation time.

### SPECIFICATIONS

#### GENERAL INFO

Size: Deep  
Product Series: Slater  
Type: Box  
Special Features: Quick/Click

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: No  
CUL Listing No: No  
cULus: No  
cURus: No  
Federal Spec: No  
UL Listing No: Yes

UN SPSC: 39121308  
UR: No

#### **DIMENSIONS**

Depth (US): 3.375  
Length (US): 3.75  
Width (US): 2.25  
Volume: 22.5

#### **TECHNICAL INFORMATION**

Material: Plastic  
Mounting: Captive Mounting Nails

#### **BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: UNITED STATES OF AMERICA  
Buy American Act Status: Buy American Act Compliant





## SWITCH & OUTLET BOX

S122R | [Pass & Seymour](#)

### FEATURES & BENEFITS

Durable, impact-resistant thermoplastic boxes complemented by innovative extras that cut installation time. Single Gang, Deep Switch and Outlet Box. Extra deep for dimmers, GFCIs and thermostats, yet suitable for 2x4 construction. Two Quick/Click Entries, 100 Pack.



- Quick/Click feature secures devices quickly and easily.
- Does not strip when over-torqued.
- Durable, impact-resistant thermoplastic box.
- Innovative extras that cut installation time.

### SPECIFICATIONS

#### GENERAL INFO

Size: Deep  
Product Series: Slater  
Type: Box  
Special Features: Quick/Click

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
CSA Listing Info: No  
CUL Listing No: No  
cULus: No  
cURus: No  
Federal Spec: No  
UL Listing No: Yes

UN SPSC: 39121308  
UR: No

#### **DIMENSIONS**

Depth (US): 3.375  
Length (US): 3.75  
Width (US): 2.25  
Volume: 22.5

#### **TECHNICAL INFORMATION**

Material: Plastic  
Mounting: Captive Mounting Nails

#### **BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: UNITED STATES OF AMERICA  
Buy American Act Status: Buy American Act Compliant

