



## DEEP OLD WORK SWITCH & OUTLET BOX WITH QUICK/CLICK

S122W | [Pass & Seymour](#)

### FEATURES & BENEFITS

Single gang, deep old work switch and outlet box with Quick/Click and Swing-Bracket for mounting, adjusts from 1 1/4" down to 1/8". It has two Auto/Clamps for each end. It has a durable, impact-resistant thermoplastic box. The metal swing bracket is for quick mounting in existing walls. 50 pack.



- Quick/Click feature secures devices quickly and easily.
- Does not strip when over-torqued.
- 2 Auto/Clamps on each end eliminate the need for separate cable clamps.
- Swing bracket adjusts from 1 1/4 inch to 1/8 inch.

### SPECIFICATIONS

#### GENERAL INFO

Size: Deep  
Product Series: Slater  
Type: Switch, Outlet Box  
Special Features: Quick/Click, Auto Clamps

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
UN SPSC: 39121308

#### DIMENSIONS

Depth (US): 3.5

Length (US): 3.75  
Width (US): 2.3125  
Volume: 22.0

#### TECHNICAL INFORMATION

Material: Plastic

#### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA  
Buy American Act Status: Buy American Act Compliant





## DEEP OLD WORK SWITCH & OUTLET BOX WITH QUICK/CLICK

S122W | [Pass & Seymour](#)

### FEATURES & BENEFITS

Single gang, deep old work switch and outlet box with Quick/Click and Swing-Bracket for mounting, adjusts from 1 1/4" down to 1/8". It has two Auto/Clamps for each end. It has a durable, impact-resistant thermoplastic box. The metal swing bracket is for quick mounting in existing walls. 50 pack.



- Quick/Click feature secures devices quickly and easily.
- Does not strip when over-torqued.
- 2 Auto/Clamps on each end eliminate the need for separate cable clamps.
- Swing bracket adjusts from 1 1/4 inch to 1/8 inch.

### SPECIFICATIONS

#### GENERAL INFO

Size: Deep  
Product Series: Slater  
Type: Switch, Outlet Box  
Special Features: Quick/Click, Auto Clamps

#### LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes  
UN SPSC: 39121308

#### DIMENSIONS

Depth (US): 3.5

Length (US): 3.75  
Width (US): 2.3125  
Volume: 22.0

#### TECHNICAL INFORMATION

Material: Plastic

#### BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA  
Buy American Act Status: Buy American Act Compliant

