



DEEP OLD WORK SWITCH & OUTLET BOX WITH QUICK/CLICK

S122W | [Pass & Seymour](#)

FEATURES & BENEFITS

Single gang, deep old work switch and outlet box with Quick/Click and Swing-Bracket for mounting, adjusts from 1 1/4" down to 1/8". It has two Auto/Clamps for each end. It has a durable, impact-resistant thermoplastic box. The metal swing bracket is for quick mounting in existing walls. 50 pack.



- Quick/Click feature secures devices quickly and easily.
- Does not strip when over-torqued.
- 2 Auto/Clamps on each end eliminate the need for separate cable clamps.
- Swing bracket adjusts from 1 1/4 inch to 1/8 inch.

SPECIFICATIONS

GENERAL INFO

Size: Deep
Product Series: Slater
Type: Switch, Outlet Box
Special Features: Quick/Click, Auto Clamps

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
UN SPSC: 39121308

DIMENSIONS

Depth (US): 3.5

Length (US): 3.75
Width (US): 2.3125
Volume: 22.0

TECHNICAL INFORMATION

Material: Plastic

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA
Buy American Act Status: Buy American Act Compliant





DEEP OLD WORK SWITCH & OUTLET BOX WITH QUICK/CLICK

S122W | [Pass & Seymour](#)

FEATURES & BENEFITS

Single gang, deep old work switch and outlet box with Quick/Click and Swing-Bracket for mounting, adjusts from 1 1/4" down to 1/8". It has two Auto/Clamps for each end. It has a durable, impact-resistant thermoplastic box. The metal swing bracket is for quick mounting in existing walls. 50 pack.



- Quick/Click feature secures devices quickly and easily.
- Does not strip when over-torqued.
- 2 Auto/Clamps on each end eliminate the need for separate cable clamps.
- Swing bracket adjusts from 1 1/4 inch to 1/8 inch.

SPECIFICATIONS

GENERAL INFO

Size: Deep
Product Series: Slater
Type: Switch, Outlet Box
Special Features: Quick/Click, Auto Clamps

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
UN SPSC: 39121308

DIMENSIONS

Depth (US): 3.5

Length (US): 3.75
Width (US): 2.3125
Volume: 22.0

TECHNICAL INFORMATION

Material: Plastic

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA
Buy American Act Status: Buy American Act Compliant

