



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685



## **S28684 4W Led E11 Mini 30K Clear Candelabra Base 120-130V**

*Satco*

Catalog Number	S28684
Manufacturer	Satco
Description	Led Lamp, Dimmable Type; 2-3/8 Inch; Ul, Etl (Canada and Us), Cec Approval; 120 to 130 Volt Ac 50/60 Hertz Voltage Rating; 1/2 Inch Diameter; 4 Watt Wattage; Led Lamp; E11 Mini Candelabra Base Type; 25000 Life In Hour; 480 Lumen Intensity; 3000
Weight per unit	0.0300 (lbs/each)
Product Category	Led Specialty Lamps & Modules

### **Features**

Beam Spread Angle	360 Degree
Glass Finish	CLEAR
Intensity	480 LUMEN
Item	LED Lamp
Voltage Rating	120 to 130 Volt AC 50/60 Hertz
Wattage	4 Watt

### **Material, Color, and Finish**

Base Type	E11 Mini Candelabra
Color Rendering Index	80 A
Color Temperature in Kelvin	3000
Glass Color	WARM WHITE

### **Dimensions and Weight**

Diameter	1/2 INCH
Length	2-3/8 INCH



# ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.  
75964-0000, TX Nacogdoches  
Phone: 936-569-7941  
Fax: 936-560-4685

## Descriptions

Additional Information	RoHS Compliant
Commodity Description	LED SPECIALTY LAMPS & MODULES
Description	4W LED E11 MINI 30K CLEAR CANDELABRA BASE 120-130V
extra long description	DIMMABLE TYPE; 2-3/8 INCH; UL, ETL (CANADA AND US), CEC APPROVAL; 120 TO 130 VOLT AC 50/60 HERTZ VOLTAGE RATING; 1/2 INCH DIAMETER; 4 WATT WATTAGE; LED LAMP; E11 MINI CANDELABRA BASE TYPE; 25000 LIFE IN HOUR; 480 LUMEN INTENSITY; 3000; 80 COLOR RENDERING INDEX; CLEAR GLASS FINISH; WARM WHITE GLASS COLOR; 360 DEGREE BEAM SPREAD ANGLE; OMNI-DIRECTIONAL BEAM SPREAD TYPE; ROHS COMPLIANT
Long Description	LED LAMP, DIMMABLE TYPE; 2-3/8 INCH; UL, ETL (CANADA AND US), CEC APPROVAL; 120 TO 130 VOLT AC 50/60 HERTZ VOLTAGE RATING; 1/2 INCH DIAMETER; 4 WATT WATTAGE; LED LAMP; E11 MINI CANDELABRA BASE TYPE; 25000 LIFE IN HOUR; 480 LUMEN INTENSITY; 3000
Product Type	Led Lamp

## Manufacturer Information

Brand	Satco
GTIN	00045923286841
Manufacturers Part Number	S28684
UPC	045923286841

## Taxonomies, Classifications, and Categories

Category Description	LED SPECIALTY LAMPS & MODULES
Type	DIMMABLE

## Packaging

Carton	1
Weight Per each	0.03

## Uses, Certifications, and Standards

Approval	UL, ETL (Canada and US), CEC
Energy Star	yes