ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S38946 100W Led Temp Light 5K Integrated Cord/Plug & Hook

Satco

Catalog Number	S38946
Manufacturer	Satco
Description	100 Watt Led Hi-Lumen Temporary Hi-Bay Caged Lamp - 5000K - Integrated Cord / Plug & Hook - 120 Volts
Weight per unit	5.3 (lbs/each)
Product Category	Lighting

Features

average life	50000
Base	Plug
beam angle	360
dimmable	Non-Dimmable
lumens	10000
Material	Plastic; Steel
Power Factor	0.9
Shape	Corncob
Voltage Rating	120
Warranty	5 Year Limited - Hi-Pro
Wattage	100

Material, Color, and Finish

color rendering index (cri)	80+
color temperature	5000
Finish	ORANGE

Dimensions and Weight

Diameter	5.12
Length	5.12
Size	10.9

Descriptions

Description	100W LED TEMP LIGHT 5K INTEGRATED CORD/PLUG & HOOK
extra long description	SATCO S38946 100W/LED/HID/TEMP/5K/1
Long Description	100 Watt LED Hi-Lumen Temporary Hi-Bay Caged Lamp - 5000K - Integrated Cord / Plug & Hook - 120 Volts
Product Type	100W/Led/Hid/Temp/5K/120V
Special Features	Warranty: 5-Years ; Location Rating: Damp ; Operating Temp: -30C (-22F) to +60C (+140F) ; Material: Plastic / Steel ; Indoor Outdoor: Indoor ; Color Temp: Natural Light ; Efficacy: 100.00 LPW ; Energy Star Certified: No ; DLC Approved: False ; FCC Compliant: True ; Indoor Outdoor: Indoor ; ANSI Base: Plug ; Amps: 0.833A ; T24 Compliant: False

ELLIOTT ELECTRIC SUPPLY
We Deliver...Lower Cost, Quality Products, & Personal Service
2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Manufacturer Information

Brand	Satco
GTIN	00045923389467
Manufacturers Part Number	S38946
UPC	045923389467

Taxonomies, Classifications, and Categories

Category Description	Led Lighting
Type	Functional Lighting

Packaging

Carton	1
Package	4
Weight	3.65
Weight Per each	5.28

Uses, Certifications, and Standards

Application	LED
Operating Temperature	-30C (-22F) to a maximum of +60C (+140F)
standard	cULus - Certified