



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685



S39752 60W Led Hid Adj Panels 50K Mog Base

Satco

| | |
|------------------|---|
| Catalog Number | S39752 |
| Manufacturer | Satco |
| Description | 60 Watt Led Hid Replacement - 5000K - Mogul Extended Base - Adjustable Beam Angle - 100-277 Volts |
| Weight per unit | 2.1 (lbs/each) |
| Product Category | Lighting |

Features

| | |
|------------------|---------------------------------------|
| average life | 50000 |
| Base | EX39 |
| beam angle | 260 |
| lumens | 8.4k |
| Material | Thermo Plastic (PBT); Steel; Aluminum |
| Shape | ED28 |
| surge protection | Built-in surge protection - 4KV |
| voltage range | 277 |
| Warranty | 5 Year Limited - Hi-Pro |
| Wattage | 60 |

Material, Color, and Finish

| | |
|-------------------|-------|
| color temperature | 5000 |
| Finish | Clear |

Dimensions and Weight

| | |
|------|------|
| Size | 7.76 |
|------|------|

Descriptions

| | |
|------------------------|---|
| Description | 60W LED HID ADJ PANELS 50K MOG BASE |
| extra long description | SATCO S39752 60W/LED/HID/MB-G3/50K/ |
| Long Description | 60 Watt LED HID Replacement - 5000K - Mogul Extended Base - Adjustable Beam Angle - 100-277 Volts |
| Product Type | 60W/Led/Hid/MB-G3/50K/100-277V |
| Special Features | Lawful for sale in California ; Color Temperature: Natural Light ; Dimmable: Non-Dimmable ; Lamp Base: Mogul Extended ; MOL: 7.76 in. ; MOD: 4.13 in. ; Weight: 2.05 lb. ; DLC Approved |

Manufacturer Information

| | |
|---------------------------|----------------|
| Brand | Satco |
| GTIN | 00045923397523 |
| Manufacturers Part Number | S39752 |
| UPC | 045923397523 |



ELLIOTT ELECTRIC SUPPLY

We Deliver...Lower Cost, Quality Products, & Personal Service

2310 N. Stallings Dr.
75964-0000, TX Nacogdoches
Phone: 936-569-7941
Fax: 936-560-4685

Taxonomies, Classifications, and Categories

| | |
|----------------------|-------------------------------|
| Category Description | LED SPECIALTY LAMPS & MODULES |
| Type | LED HID Replacement |

Packaging

| | |
|-----------------|------|
| Carton | 1 |
| Package | 6 |
| Weight | 2.05 |
| Weight Per each | 2.05 |

Uses, Certifications, and Standards

| | |
|-----------------------|---|
| Operating Temperature | -20C (-4F) to a maximum of +65C (+149F) |
| standard | cULus Classified |