



TAMPER-RESISTANT CLOCK HANGER RECEPTACLES, RECESSED WITH SMOOTH WALL PLATE, 15A, 125V, WHITE

S3713TRW | [Pass & Seymour](#)

FEATURES & BENEFITS

Tamper-Resistant Clock Hanger Recessed Receptacle with Smooth Wall Plate 15amp 125volt, White

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles](#) page.



- Single recessed receptacle.
- Smooth wall plate.

SPECIFICATIONS

GENERAL INFO

Color: White

Type: Clock Hanger

Special Features: Clock Hanger

Style: Decorator, Smooth

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listed: Yes

CSA Standard: C22.2 No. 42

CUL Listing No: No

cULus: No

cURus: No

Federal Spec: Yes

UL Standard: UL498

UN SPSC: 39121406

UR: No

DIMENSIONS

Depth (US): 1.878"
Height (US): 4.478"
Width (US): 2.74"

TECHNICAL INFORMATION

Amps: 15A
NEMA Configuration Number: 5-15R
Volts: 125V
Volts (AC): 125
Grade Type: Specification

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant





TAMPER-RESISTANT CLOCK HANGER RECEPTACLES, RECESSED WITH SMOOTH WALL PLATE, 15A, 125V, WHITE

S3713TRW | [Pass & Seymour](#)

FEATURES & BENEFITS

Tamper-Resistant Clock Hanger Recessed Receptacle with Smooth Wall Plate 15amp 125volt, White

For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles](#) page.



- Single recessed receptacle.
- Smooth wall plate.

SPECIFICATIONS

GENERAL INFO

Color: White

Type: Clock Hanger

Special Features: Clock Hanger

Style: Decorator, Smooth

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listed: Yes

CSA Standard: C22.2 No. 42

CUL Listing No: No

cULus: No

cURus: No

Federal Spec: Yes

UL Standard: UL498

UN SPSC: 39121406

UR: No

DIMENSIONS

Depth (US): 1.878"
Height (US): 4.478"
Width (US): 2.74"

TECHNICAL INFORMATION

Amps: 15A
NEMA Configuration Number: 5-15R
Volts: 125V
Volts (AC): 125
Grade Type: Specification

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: MEXICO
Buy American Act Status: Trade Agreement Act Compliant

