

Commercial Network Wiring Innovate™ UTP & Multimedia Jack Modules




S68-LA



S58-LA



SFF-LA



S2BP-LA



SBL10-LA



PSDST-LA



PSDSC-LA

- Features**
- Universal design supports either T568A or T568B. Easy-to-read color code wiring label.
 - Front-mount, click-in design. Removes easily for quick reconfiguration. Built strong to stand up to repeated installations and removals.
 - Paired punchdown sequence makes 110-style termination fast and simple. Provides TIA/EIA-568-B.2 standards compliance.

| Catalog Number | Description | Color |
|---------------------------------|--------------------------------------------------------|------------|
| Category 6 Jack Modules | | |
| S68-BK | RJ45 Category 6, T568A/B Universal Wiring | Black |
| S68-BL | | Blue |
| S68-BR | | Brown |
| S68-G | | Green |
| S68-GRY | | Gray |
| S68-I | | Ivory |
| S68-LA | | Lt. Almond |
| S68-OR | | Orange |
| S68-P | | Purple |
| S68-RED | | Red |
| S68-W | White | |
| S68-Y | Yellow | |
| Category 5e Jack Modules | | |
| S58-BK | RJ45 Category 5e, T568A/B Universal Wiring | Black |
| S58-BL | | Blue |
| S58-BR | | Brown |
| S58-G | | Green |
| S58-GRY | | Gray |
| S58-I | | Ivory |
| S58-LA | | Lt. Almond |
| S58-OR | | Orange |
| S58-P | | Purple |
| S58-RED | | Red |
| S58-W | | White |
| S58-Y | | Yellow |
| PS58-SCTP* | | |
| Category 3 Jack Modules | | |
| S38-BK | RJ45 Category 3, T568A/B Universal Wiring | Black |
| S38-GRY | | Gray |
| S38-I | | Ivory |
| S38-LA | | Lt. Almond |
| S38-W | | White |
| USOC Jack Modules | | |
| S6U-GRY | RJ25C (RJ12) 6P/6C USOC Wiring | Gray |
| S6U-I | | Ivory |
| S6U-LA | | Lt. Almond |
| S6U-W | | White |

*Shielded for 100 ohm SCTP



S38-LA

S6U-LA

- Features**
- F connector module supports video coax cable.
 - Binding posts enable easy speaker wiring for multiroom stereo and accept both stripped conductor and banana plug connection. Red and black color coding makes it simple to ensure correct speaker wiring polarity.
 - Blank module instantly fills unused jack module spaces in wall plates.
 - ST™ and SC adapter modules let you bring fiber directly to the desktop for handling demanding, high-bandwidth applications. Available in both single- and dual-adapter models.

| Catalog Number | Description | Color |
|-------------------------------------------------|---------------------------------------------------------------------------------------|------------|
| Innovate Multimedia Modules & Blanks | | |
| SFF-GRY | F connector bulkhead for video | Gray |
| SFF-I | | Ivory |
| SFF-LA | | Lt. Almond |
| SFF-W | White | |
| S2BP-BK | 1 pair binding posts, red/positive and black/negative for speaker connection | Black |
| S2BP-I | | Ivory |
| S2BP-LA | | Lt. Almond |
| S2BP-W | | White |
| PSST-LA | ST adapter phosphor bronze sleeve | Lt. Almond |
| PSSC-LA | SC adapter phosphor bronze sleeve | Lt. Almond |
| PSDST-LA | Dual ST adapter phosphor bronze sleeve | Lt. Almond |
| PSDSC-LA | Dual SC adapter phosphor bronze sleeve | Lt. Almond |
| PSSV-LA | S-video connector | Lt. Almond |
| PS2RCA-I | RCA audio connector | Ivory |
| PS2RCA-LA | | Lt. Almond |
| PS2RCA-W | | White |
| SBL10-BK | Blank module | Black |
| SBL10-GRY | | Gray |
| SBL10-I | | Ivory |
| SBL10-LA | | Lt. Almond |
| SBL10-W | | White |
| PSBNC-LA | BNC connector | Lt. Almond |

Available vibrant colors make identification easy





Commercial Network Wiring Innovate™ UTP & Multimedia Jack Modules




S68-LA



S58-LA



SFF-LA



S2BP-LA



SBL10-LA



PSDST-LA



PSDSC-LA

- Features**
- Universal design supports either T568A or T568B. Easy-to-read color code wiring label.
 - Front-mount, click-in design. Removes easily for quick reconfiguration. Built strong to stand up to repeated installations and removals.
 - Paired punchdown sequence makes 110-style termination fast and simple. Provides TIA/EIA-568-B.2 standards compliance.

| Catalog Number | Description | Color |
|---------------------------------|--------------------------------------------------------|------------|
| Category 6 Jack Modules | | |
| S68-BK | RJ45 Category 6, T568A/B Universal Wiring | Black |
| S68-BL | | Blue |
| S68-BR | | Brown |
| S68-G | | Green |
| S68-GRY | | Gray |
| S68-I | | Ivory |
| S68-LA | | Lt. Almond |
| S68-OR | | Orange |
| S68-P | | Purple |
| S68-RED | | Red |
| S68-W | White | |
| S68-Y | Yellow | |
| Category 5e Jack Modules | | |
| S58-BK | RJ45 Category 5e, T568A/B Universal Wiring | Black |
| S58-BL | | Blue |
| S58-BR | | Brown |
| S58-G | | Green |
| S58-GRY | | Gray |
| S58-I | | Ivory |
| S58-LA | | Lt. Almond |
| S58-OR | | Orange |
| S58-P | | Purple |
| S58-RED | | Red |
| S58-W | | White |
| S58-Y | | Yellow |
| PS58-SCTP* | | |
| Category 3 Jack Modules | | |
| S38-BK | RJ45 Category 3, T568A/B Universal Wiring | Black |
| S38-GRY | | Gray |
| S38-I | | Ivory |
| S38-LA | | Lt. Almond |
| S38-W | | White |
| USOC Jack Modules | | |
| S6U-GRY | RJ25C (RJ12) 6P/6C USOC Wiring | Gray |
| S6U-I | | Ivory |
| S6U-LA | | Lt. Almond |
| S6U-W | | White |

*Shielded for 100 ohm SCTP



S38-LA

S6U-LA

- Features**
- F connector module supports video coax cable.
 - Binding posts enable easy speaker wiring for multiroom stereo and accept both stripped conductor and banana plug connection. Red and black color coding makes it simple to ensure correct speaker wiring polarity.
 - Blank module instantly fills unused jack module spaces in wall plates.
 - ST™ and SC adapter modules let you bring fiber directly to the desktop for handling demanding, high-bandwidth applications. Available in both single- and dual-adapter models.

| Catalog Number | Description | Color |
|-------------------------------------------------|---------------------------------------------------------------------------------------|--------------|
| Innovate Multimedia Modules & Blanks | | |
| SFF-GRY | F connector bulkhead for video | Gray |
| SFF-I | | Ivory |
| SFF-LA | | Light Almond |
| SFF-W | | White |
| S2BP-BK | 1 pair binding posts, red/positive and black/negative for speaker connection | Black |
| S2BP-I | | Ivory |
| S2BP-LA | | Light Almond |
| S2BP-W | | White |
| PSST-LA | ST adapter phosphor bronze sleeve | Light Almond |
| PSSC-LA | SC adapter phosphor bronze sleeve | Light Almond |
| PSDST-LA | Dual ST adapter phosphor bronze sleeve | Light Almond |
| PSDSC-LA | Dual SC adapter phosphor bronze sleeve | Light Almond |
| PSSV-LA | S-video connector | Light Almond |
| PS2RCA-I | RCA audio connector | Ivory |
| PS2RCA-LA | | Light Almond |
| PS2RCA-W | | White |
| SBL10-BK | Blank module | Black |
| SBL10-GRY | | Gray |
| SBL10-I | | Ivory |
| SBL10-LA | | Light Almond |
| SBL10-W | | White |
| PSBNC-LA | BNC connector | Light Almond |

Available vibrant colors make identification easy

