
SWITCH & OUTLET BOX

S468RAC | [Pass & Seymour](#)



FEATURES & BENEFITS

Four Gang Switch and Outlet Box. Captive Mounting Nails on Each End with Quick/Click Entries . Rear Stabilizing bar virtually eliminates inward movement. Six Auto/Clamps each end. 25 Pack.



- Quick/Click feature secures devices quickly and easily.
- Does not strip when over-torqued.
- 6 Auto/Clamps on each end eliminate the need for separate cable clamps.
- Easy installation, rectangular cutout.
- Durable, impact-resistant thermoplastic box.
- Innovative extras that cut installation time.

SPECIFICATIONS

GENERAL INFO

Product Series: Slater

Type: Box

Special Features: Quick/Click, Auto Clamps, Rear Stabilizing Bar

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: No

CUL Listing No: No

cULus: No

cURus: No

Federal Spec: No

UL Listing No: Yes
UN SPSC: 39121308
UR: No

DIMENSIONS

Depth (US): 3
Length (US): 3.8125
Width (US): 7.8125
Volume: 68.0

TECHNICAL INFORMATION

Material: Plastic
Mounting: Captive Mounting Nails

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA
Buy American Act Status: Buy American Act Compliant



SWITCH & OUTLET BOX

S468RAC | [Pass & Seymour](#)



FEATURES & BENEFITS

Four Gang Switch and Outlet Box. Captive Mounting Nails on Each End with Quick/Click Entries . Rear Stabilizing bar virtually eliminates inward movement. Six Auto/Clamps each end. 25 Pack.



- Quick/Click feature secures devices quickly and easily.
- Does not strip when over-torqued.
- 6 Auto/Clamps on each end eliminate the need for separate cable clamps.
- Easy installation, rectangular cutout.
- Durable, impact-resistant thermoplastic box.
- Innovative extras that cut installation time.

SPECIFICATIONS

GENERAL INFO

Product Series: Slater

Type: Box

Special Features: Quick/Click, Auto Clamps, Rear Stabilizing Bar

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes

CSA Listing Info: No

CUL Listing No: No

cULus: No

cURus: No

Federal Spec: No

UL Listing No: Yes
UN SPSC: 39121308
UR: No

DIMENSIONS

Depth (US): 3
Length (US): 3.8125
Width (US): 7.8125
Volume: 68.0

TECHNICAL INFORMATION

Material: Plastic
Mounting: Captive Mounting Nails

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA
Buy American Act Status: Buy American Act Compliant

